

[All Products](#) | [Cable Ties Stainless Steel](#) | [Stainless Steel Systems](#) | [Stainless Steel Cable Ties](#) |

**PCS Cushion Sleeve**



Black vinyl sleeving slips on *Pan-Steel*™ steel ties and custom length banding and is used on applications requiring improved gripping on non-resilient objects, separation between dissimilar metals, and added bundle protection. Can be used indoors or outdoors (excellent ultraviolet resistance, good resistance to petroleum, and many chemicals). Provides full separation between the ties and the material to which you are fastening.

- Operating Temperature Range 41°F – 167°F (5°C – 75°C)
- Supplied in 100 ft (30.5m) Reels

Part Number	<b>PCSS-CR</b>
Product Family	PCS Cushion Sleeve
Part Description	Used with standard cross section ties or custom length banding system
Length (ft)	100
Length (M)	30.50
Width (in)	0.31
Width (mm)	0.87
UOM	PC
Std. Pkg. Qty.	1
Min. Order Qty	1
Qty	<input type="text" value="0"/>

[Update Bill of Material](#)