

4

3


2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS   |   |         |        |
|-----|------|-------------|---|---------|--------|
| P   | LTR  | DESCRIPTION | DATE                                    | DWN     | APVD   |
| G   | 14   | L1          | DRAFT. CORRECTION (3--2 SHOULD BE 2--2) | 08AUG96 | MLE SB |

|                            |                            |                            |
|----------------------------|----------------------------|----------------------------|
| <b>AMP</b><br>WIRE RANGE   | E13288                     | LR7189<br>Certified        |
| 12-10<br>SOLID OR STRANDED | 12-10<br>SOLID OR STRANDED | 12-10<br>SOLID OR STRANDED |



1. WIRE INSUL DIA,  
3.81-5.84 [.150-.230]

| QTY  | PACKAGE TYPE     | PART NO   |
|------|------------------|-----------|
| 25   | LOOSE PIECE, BAG | 8-34072-5 |
| 5    | LOOSE PIECE, BLS | 8-34072-4 |
| 100  | LOOSE PIECE, BOX | 8-34072-1 |
| 1500 | ON TAPE, REEL    | 2-34072-2 |
| 500  | LOOSE PIECE      | 34072     |

|  |  |  |  |   |                              |  |
|--|--|--|--|---|------------------------------|--|
| AMP INCORPORATED<br>CUSTOMER SERVICE SYSTEM                                      |  | MAX RECOMMENDED OPERATING TEMPERATURE:<br>90°C [194°F]   | THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.<br>IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. |   | DWN<br>M ELLIS<br>19JUL95    | <b>AMP</b> AMP Incorporated<br>Harrisburg, PA 17105-3608 |
| FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS | PRODUCT INFORMATION CENTER<br>1-800-522-6752 |  | DIMENSIONS:<br>mm [in]   | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                | CHK<br>C PRESNELL<br>19JUL95 |  |
| FOR APPLICATION TOOLING INFORMATION  | TOOLING ASSISTANCE CENTER<br>1-800-722-1111  | VOLTAGE RATING:<br>600V MAX<br>1000V (FIXTURES OR SIGNS) |  | 0 PLC ±-<br>1 PLC ±-<br>2 PLC ±-<br>3 PLC ±-<br>4 PLC ±-<br>ANGLES ±- | PRODUCT SPEC<br>UL486A       | SPLICE, BUTT, PLASTI-GRIP™,<br>WIRE SIZE, 12-10 AWG      |
| FOR ORDER ENTRY  | 1-800-526-5142                               | CIRCULAR MIL AREA:<br>2.62mm²-6.64mm² [5180-13100]       | MATERIAL<br>BODY, CU ASTM B 152<br>SLV, PVC, COLOR, YELLOW   | FINISH<br>TIN PLATE<br>PER MIL-T-10727                                | APPLICATION SPEC<br>-        |  |
|  |  |  |  |   | WEIGHT<br>-                  | CAGE CODE<br>00779                                       |
|  |  |  |  |   | CUSTOMER DRAWING             | DRAWING NO<br>C-34072                                    |
|  |  |  |  |   |                              | SCALE<br>4:1   |
|  |  |  |  |   |                              | SHEET<br>1 OF 1  |
|  |  |  |  |   |                              | REV<br>L1  |

AMP 1470-19 REV 09MAY94