

Product Datasheet 2U Energy Saving Lamps



2U 9W B22	9W (40W)	Lamp BC Fitting	45 Lumens
2U 11W B22	11W (60W)	Lamp BC Fitting	45 Lumens
2U 15W B22	15W (75W)	Lamp BC Fitting	45 Lumens
2U 18W B22	18W (100W)	Lamp BC Fitting	45 Lumens
2U 9W E27	9W (40W)	Lamp ES Fitting	45 Lumens
2U 11W E27	11W (60W)	Lamp ES Fitting	45 Lumens
2U 15W E27	15W (75W)	Lamp ES Fitting	45 Lumens
2U 18W E27	18W (100W)	Lamp ES Fitting	45 Lumens

Available as:

- Type: Warm light or Daylight
- Wattage: 9W, 11W, 15W and 18W
- Fitting: BC (B22), ES (E27) and SES (E14)

Features

- Energy Rating 'A'. Up to 80% energy saving compared to traditional bulbs by using less electricity to reach the equivalent brightness:
 - 9 WATTS = 40 WATTS for a conventional bulb
 - 11 WATTS = 60 WATTS for a conventional bulb
 - 15 WATTS = 75 WATTS for a conventional bulb
 - 18 WATTS = 100 WATTS for a conventional bulb
- Lamp life up to 8000 hours (8 times longer than conventional GLS lamps)
- Not suitable for dimming, electronic switches, photocells, timing devices, dusk to dawn sensors.
- Instant start up
- No flicker and no filament to burn out!
- Switching does not reduce lamp life
- Excellent colour render
- RoHS Compliant