

SKINTOP® Accessories metric

Glass fibre reinforced locknuts

SKINTOP® GMP-GL-M Hexagonal locknuts of polyamide, glass fibre reinforced

Hexagonal polyamide counter nut, glass fibre-coated with collar. The counter nuts with metric thread are matched with our SKINTOP® cable glands in quality and design.



Note

SKINTOP® GMP-GL-M also available without collar.
UL-approved only on use with the UL-approved SKINTOP® plastic cable glands.

Technical Data	Material:	Standard colour:	Temperature range:	On request:	Note:
SKINTOP® GMP-GL-M	Polyamide, glass fibre-coated	RAL 7001 silver grey RAL 7035 light grey RAL 9005 black/UV-resistant	-20°C to +100°C	available without collar	Data sheet on request

Part number	Thread size M	Wrench size	PU pieces
SKINTOP® GMP-GL-M silver grey			
5311 9000	12 x 1,5	17	100
5311 9010	16 x 1,5	22	100
5311 9020	20 x 1,5	27	100
5311 9030	25 x 1,5	34	100
5311 9040	32 x 1,5	41	100
5311 9050	40 x 1,5	50	25
5311 9060	50 x 1,5	60	25
5311 9070	63 x 1,5	75	25
SKINTOP® GMP-GL-M black			
5311 9100	12 x 1,5	17	100
5311 9110	16 x 1,5	22	100
5311 9120	20 x 1,5	27	100
5311 9130	25 x 1,5	34	100
5311 9140	32 x 1,5	41	100
5311 9150	40 x 1,5	50	25
5311 9160	50 x 1,5	60	25
5311 9170	63 x 1,5	75	25
SKINTOP® GMP-GL-M light grey			
5311 9003	12 x 1,5	17	100
5311 9013	16 x 1,5	22	100
5311 9023	20 x 1,5	27	100
5311 9033	25 x 1,5	34	100
5311 9043	32 x 1,5	41	100
5311 9053	40 x 1,5	50	25
5311 9063	50 x 1,5	60	25
5311 9073	63 x 1,5	75	25