

# HP Deskjet 1280 Printer



Affordable and proven versatile printing for output on larger format media up to A3+ with this reliable, easy-to-use colour inkjet printer. The HP Deskjet 1280 Printer delivers professional print quality and performance on a wide choice of media.

**The HP Deskjet 1280 Printer is ideal for creative individuals in the home, small business, architectural and design environments, who need to easily create large-size concept proofs, maps, plans, charts, posters, and many more.**

**Versatile and convenient printing on various media types and sizes from A6 up to A3+.**

- Create whatever professional quality documents you need from everyday business correspondence to high-impact marketing materials on larger format media up to A3+.
- The choice of media has never been greater: from standard company stationery to thick card stock, photo media, and more.
- Heavy media up to 280 g/m<sup>2</sup> prints smoothly and reliably using the straight through paper path at the back of the printer.
- Flexible media handling with an extendable high-capacity input tray of up to 150 sheets.

**Enjoy outstanding print quality without sacrificing all-around performance.**

- Achieve sharp black text at up to 14 ppm and professional-quality colour documents at up to 11 ppm.
- Enjoy creative, large format printing in vibrant, natural colour, and never worry about image quality with HP Photorec III precision technology, or up to 4800-optimised dpi.
- Share the performance, with an optional HP Jetdirect External Print Server you can easily share the versatile capabilities of the HP Deskjet 1280 Printer.

**Robust, reliable and simple-to-use great value printer.**

- Robust printing with a duty cycle of up to 5,000 pages per month.
- Effortlessly reduce or enlarge documents from A6 to A3+ with HP's sophisticated Smart Software.
- The media width sensor prevents misprinted pages by alerting when the paper loaded does not match the size selected in the printer driver.
- The on-screen ink-level indicator lets you know when it's time to replace your ink cartridges.
- Print Cancel button halts unwanted print jobs immediately, saving time and money.

## Technical specifications

<b>Print technology</b>	HP Thermal Inkjet			
<b>Print speed</b> (Up to # pages per minute)	<b>Document type</b>	<b>Draft</b>	<b>Normal</b>	<b>Best</b>
	Black text A4	14	7	4
	Black text A3	7.9	3.9	2.8
	Mixed text/colour graphics A4	11	5.5	2
	Mixed text/colour graphics A3	5.4	2.7	1.4
	(Approximate figures. Exact print speed will vary depending on the system configuration, software program and document complexity. Speed specifications reflect current industry testing methods.)			
<b>Processor speed</b>	32 MHz			
<b>Print quality</b>	Black: up to 600 x 600 dpi Colour: HP Photoret III precision technology, up to 4800 x 1200-optimised dpi colour printing on premium photo paper, 1200 x 1200 input dpi			
<b>Operating systems compatibility</b>	Windows® 98, NT 4.0, Me, 2000, XP; Mac OS 10.1.5 and above			
<b>Recommended system requirements</b>	Microsoft® Windows® 98: Pentium® 266 MHz, 32 MB RAM, 100 MB free hard disk space; Windows NT® 4.0: Pentium 266 MHz, 64 MB RAM, 100 MB free hard disk space; Windows Me: Pentium 266 MHz, 32 MB RAM, 100 MB free hard disk space; Windows 2000: Pentium 300 MHz, 64 MB RAM, 100 MB free hard disk space; Windows XP: Pentium 300 MHz, 128 MB RAM, 100 MB free hard disk space			
<b>Memory</b>	8 MB			
<b>Printer languages</b>	HP PCL 3 Enhanced			
<b>Typefaces/fonts</b>	8 built-in fonts, 4 each in portrait and landscape orientations: CG Times, CG Times Italic, Courier, Courier Italic, Letter Gothic, Letter Gothic Italic, Univers, Univers Italic			
<b>Duty cycle</b>	Up to 5,000 pages per month			
<b>Media types</b>	Paper (plain, multipurpose, inkjet, photo, banner), envelopes, transparencies, labels, greeting cards, professional brochure (matte and glossy), iron-on transfers			
<b>Maximum print area</b>	319.8 x 1254.3 mm			
<b>Print margins</b>	A4 Bottom 12 mm, Left 6 mm, Right 6 mm, Top 3 mm			
<b>Media handling</b>	<b>Input</b>	<b>Capacity</b>	<b>Weight</b>	<b>Size</b>
	Tray 1	Up to 150 sheets	60 to 135 g/m <sup>2</sup> using primary paper path, envelopes: 70 to 90 g/m <sup>2</sup> , cards: 100 to 200 g/m <sup>2</sup> , any media: up to 280 g/m <sup>2</sup> using straight through paper path at the back of the printer (manual feed)	A6, A5, A4, A3, A3+, B5, B4, index, cards greeting cards, labels, banners, envelopes, letter, legal, executive; custom: 102 x 152 to 330 x 1270 mm
	<b>Output:</b>	Up to 50 sheets		
	<b>Duplex:</b>	Manual (driver support provided)		
<b>Paper handling</b>	150-sheet input tray, 50-sheet output tray, front 10-sheet paper feed, manual single-sheet feed straight through rear path for thick media			
<b>Power</b>	<b>Requirements:</b>	Input voltage 100 to 240 VAC (± 10%), 50/60 Hz (± 3 Hz)		
	<b>Supply type:</b>	Internal universal power supply		
	<b>Consumption:</b>	1 watt maximum (off), 11.3 watts maximum (non-printing), 47.7 watts maximum (printing)		
<b>Interface and connectivity</b>	USB 2.0 full speed port, IEEE 1284-compliant bidirectional parallel port Optional: HP Jetdirect External Print Servers			
<b>Control panel</b>	"Power" button, "Cancel" button, and "Resume" button, LED ink level indicator			
<b>Smart software features</b>	Resizing, tiling, booklet, handout (N-up printing), manual duplex, banner, mirror image, watermark, optimised for fax, print preview, sepia, quick sets			
<b>Dimensions (w x d x h)</b>	Out of package: 593 x 381 x 233 mm; packaged: 670 x 320 x 480 mm			
<b>Weight</b>	Out of package: 10 kg; packaged: 12.4 kg			
<b>Operating environment</b>	Environmental ranges: Operating temperature: 5 to 40° C, recommended operating temperature: 15 to 35° C, operating humidity: 10 to 80% RH, recommended operating humidity: 20 to 80% RH, storage temperature: -40 to 60° C, storage humidity: 10 to 80% RH. Noise level per ISO 9296, sound power: LwAd 5.8 B(A), sound pressure: LpAm 47 dB(A)			
<b>Certifications</b>	Safety certifications: CE (European Union), TÜV-GS (Germany), B mark (Poland), CCC S&E (China), CSA (Canada), PSB (Singapore), UL (USA), NOM-NYCE (Mexico), KTL Mark (Korea). EMC certifications: CE (European Union), GOST (Russia), FCC Title 47 CFR Part 15 Class B (USA), ICES (Canada), CTICK (Australia and New Zealand), BSMI (Taiwan), MIC Mark (Korea). Energy Star®			
<b>Warranty</b>	One-year limited warranty			

## Ordering information

**C8173A** HP Deskjet 1280 Printer, power cord, black print cartridge (42 ml), tri-colour print cartridge (38 ml), printer software on CD-ROM, getting started guide

### Accessories

**C6518A** HP USB cable, 2 m  
**C2951A** HP IEEE-1284/B-compliant bi-directional parallel cable, 2 m  
**C2950A** HP IEEE-1284/B-compliant bi-directional parallel cable, 3 m

### Supplies

**51645AE** HP 45 Black Inkjet Print Cartridge (42 ml)  
**51645GE** HP 45 Black Inkjet Print Cartridge (21 ml)  
Available in the UK, France and Ireland only  
**C6578AE** HP 78 Tri-colour Inkjet Print Cartridge (38 ml)  
**C6578DE** HP 78 Tri-colour Inkjet Print Cartridge (19 ml)

### Media

**C1825A/C1858A** HP Bright White Inkjet Paper, A4/A3 (500/250 sheets)  
**C6818A/C6821A** HP Superior Inkjet Paper, 180 glossy, A4/A3 (50 sheets)  
**Q2525A** HP Superior Inkjet Paper, 180 glossy, tri-fold, A4 (50 sheets)  
**Q1991A/Q1992A** HP Premium Photo Paper, glossy, 10 x 15 cm (20/60 sheets)  
**C7040A** HP Premium Photo Paper, glossy, A4 (50 sheets)  
**Q1980A** HP Premium Plus Photo Paper, glossy, 10 x 15 cm (60 sheets)  
**C6832A/Q5496A** HP Premium Plus Photo Paper, glossy, A4/A3 (20 sheets)  
**Q2508A** HP Premium Plus Photo Paper, satin-matt, 10 x 15 cm (60 sheets)  
**C6951A** HP Premium Plus Photo Paper, satin-matt, A4 (20 sheets)  
**C3832A** HP Premium Transparency Film, A4 (20 sheets)  
**C7891A** HP Photo Paper, glossy, 10 x 15 cm (20 sheets)  
**C7897A** HP Photo Paper, glossy, A4 (50 sheets)  
**C1821A** HP Banner Paper, A4 (5 banners of 20 sheets)  
**C6042A** HP Matt Greeting Cards, white, quarter-fold, A4 (20 sets)  
**C6829A** HP Textured Greeting Cards, cream, half-fold, A4 (20 sets)  
**Q6551A/Q6560A** HP Labels  
**Q6593A/Q6594A** HP Professional Inkjet Paper 120 matt, A4/A3 (200/100 sheets)

### Service & support

**H3680A/E** HP Care Pack, next business day on-site, 3 years  
**H3819PA/PE** HP Care Pack, post warranty next business day on-site, 1 year  
**H3110A/E** Installation and Network Configuration

<http://www.hp.com>

For more information, please call your local HP sales office or representative: **Austria:** 0800 242 242, **Algeria:** (0)61 56 45 43, **Bahrain:** 800 728, **Belgium:** (078) 15 20 30 (0.0496€/min), **Bulgaria:** (+359) 2960 1940, **Croatia:** (+385 1) 60 60 200, **Czech republic:** (00 420) 261 108 108 (Prague), **Denmark:** +45 4812 1000, **Egypt:** 532 5222, **Estonia:** (+372) 6813 823, **Finland:** (+358) 0205 350, **France:** 0 826 800 400, **Germany:** 0180 5 665 775 (Business Products) and 0180 5 652 180 (Consumer Products) (12 Cent/min – fixed network), **Greece:** (01) 678 96 00, **Hungary:** (+36) 1 382-1111, **Iceland:** (354) 570 1000, **Ireland:** + 353 1 6158200, **Israel:** (972) 9-830 4848, **Italy:** (02) 92121, **Kazakhstan:** +7 (3272) 980 824, **Latvia:** 800 80 12, **Lithuania:** 8 800 10000 or +370 5 2103333, **Luxembourg:** (+352) 263 160 34, **Middle East:** 00971 4 883 4427, **Morocco (African Region):** +212 22 40 47 47, **Netherlands:** (020) 5476666, **Norway:** +47 08800, **Poland:** infolinia 0-800 122 622, **Portugal:** 808 206 001, **Romania:** (+401) 205 3300, **Russia:** +7 (095) 797 35 00, **Saudi Arabia:** 800 124 4646, **Serbia/Montenegro:** +381 11 201 99 00, **Slovakia:** +421-250222111, **Slovenia:** +3861 2307 420, **South Africa:** 0800 118 883, **Spain:** (91) 634 88 00, **Sweden:** (08) 444 2000, **Switzerland:** 0848 88 44 66, **Tunisia:** 71 891 222, **Turkey:** +90 (212) 444 71 71, **UAE:** 8004910, **UK:** 08705 474747, **Ukraine:** +380 44 490 61 20.



©2005 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP Products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Published in EMEA 02/05 5982-9925EEE