

## T<sup>®</sup>-Stripper Wire Strippers

IDEAL's T<sup>®</sup>-Strippers have been the industry standard for almost 50 years. Designed for stripping, holding and twisting wires, T<sup>®</sup>-Strippers are lightweight and easy to use.



▶ 45-120-341

### FEATURES

- Form-ground, knife-type blades for accurate, easy stripping without nicking insulation
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength
- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Corrosion-resistant, black oxide finish
- Tough steel construction

### FEATURES

- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured, no-slip sleeves provide a sure, easy grip

## Reflex<sup>™</sup> Premium T<sup>®</sup>-Stripper



▶ 45-425-341

## Kinetic<sup>™</sup> Reflex<sup>™</sup> T<sup>®</sup>-Stripper



▶ 45-915

### FEATURES

- Non-slip Santoprene<sup>™</sup> textured grips
- Plier nose for holding and twisting wires
- Slide lock for safety and storage
- Thumb and finger valley makes stripping easier and more accurate
- Ergonomic design for maximum comfort
- "Shear-Cut<sup>™</sup>" bolt cutters

### Catalogue Information

Description	Solid	Stranded	Cat. No.
T <sup>®</sup> -Stripper Wire Stripper-Metric		0.75-6mm <sup>2</sup>	45-120-341
T <sup>®</sup> -Stripper Wire Stripper-Metric		0.5-4mm <sup>2</sup>	45-125-341
Reflex <sup>™</sup> Premium T <sup>®</sup> -Stripper-Metric		0.5-4mm <sup>2</sup>	45-425-341
Kinetic <sup>™</sup> Reflex <sup>™</sup> T <sup>®</sup> -Stripper	1.0 mm <sup>2</sup> -4.00 mm <sup>2</sup>	2.5 mm <sup>2</sup> -0.5mm <sup>2</sup>	45-915
Kinetic <sup>™</sup> Reflex <sup>™</sup> T <sup>®</sup> -Stripper	10.0 mm <sup>2</sup> -2.5 mm <sup>2</sup>	1.0 mm <sup>2</sup> -0.5 mm <sup>2</sup>	45-918