

Professional Digital Multimeter
True RMS with Optical PC Interface

- 10,000 Count
- RS232 Data Output
- Backlight
- 750V True RMS AC+DC 1000V DC
- 10 Amps AC+DC/DC
- Temperature
- Capacitance
- Resistance
- Continuity Beeper
- Frequency
- Peak Hold
- Analog Bargraph

Measurement Ranges

DC volts ranges: 1000 mV, 10 V, 100 V, 1000 V

AC volts (True-RMS AC, AC+DC) ranges: 1000 mV, 10 V, 100 V, 750 V

DC amps (Fused) ranges: 100 μ A, 1000 μ A, 10 mA, 100 mA, 400 mA, 10 A

AC amps (True-RMS AC, AC+DC) ranges: 100 μ A, 1000 μ A, 10 mA, 100 mA, 400 mA, 10 A

Resistance ranges: 1000 Ω , 10 Ω , 100 Ω , 1000 Ω , 10 M Ω , 40 M Ω

Capacitance ranges: 40 nF, 400 nF, 4 μ F, 40 μ F, 400 μ F

Temperature ranges: -20 $^{\circ}$ C ~ 1300 $^{\circ}$ C, -4 $^{\circ}$ F ~ 2372 $^{\circ}$ F

DC 4~20 mA current range: 0 ~ 100 %

Frequency ranges: 100 Hz, 1000 Hz, 10 kHz, 100 kHz, 1000 kHz, 10 MHz

Duty cycle range: 0 to 90 %

dBm ranges: -13 to +50 dBm

Continuity-Audible indication: < 40W