

# 12.1" TFT LCD Monitor



## Specifications

LCD	12.1" TFT LCD	Signal Connector	VGA 1PCS
Display Size	246(L) x 184.5(W)mm		BNC 2PCS
Pixel Pitch	0.3075(H) x 0.3075(V)mm		AUDIO 2PCS
Display Mode (VGA)	VGA 720 x 400 (70 Hz)	OSD	Colour, Adjust, OSD ,Function, Sound
	VGA 640 x 480 (60/72/75 Hz)	Plug & Play	DDC1 / 2B
	SVGA 800 x 600(60/72/75Hz)	Audio System	0.7W / Per channel
Max. Resolution	800 x 600	Power Adapter	Input AC 100-240V, 50-60Hz, Output DC 12V/1.5A
Display Colour	262K	Operating Conditions	0°C ~ 40°C
Contrast Rate	300:1	Storage Conditions	20% ~ 80% Humidity
Brightness	250 Cd/ m2		-20°C ~ 60°C
Response	25ms	Size (LxWxH)	10% ~ 90% Humidity
Viewing Angle (CR≥10)	H 120° V 100°	Net weight	320x160x320mm
Input Signal	VGA: RGB. Analog 0.7V VIDEO: PAL/NTSC		2.7Kg