




© COPYRIGHT — BY —


REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APR
V1	REVISED PER ECO-11-005294	5APR11	RK	HMR



⚠️ NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA AND WIRE BARREL.



⚠️ NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA.



GOLD	⚠️ 3	.012 PH. BRZ	60617-6
GOLD	⚠️ 1	BRASS	-5
TIN		PH. BRZ	-4
TIN		.012 BRASS	60617-1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±

CONTRACT NO  
DR *M. FEHER 11-16-79*

CHK *D.S. Heide 1/4 190*

APPD *D. ... 1-7-80*

MATERIAL  
SEE TABLE

FINISH  
SEE TABLE

WIRE RANGE  
24-18 AWG

INSULATION DIA  
.100 MAX



NAME  
SOCKET, LOOSE PIECE, COMMERCIAL MATE-N-LOK

SIZE **A** CODE IDENT NO **00779** DRAWING NO **60617**

SCALE — SHEET —