



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REV, RDRW, & SM PKG PER 0720-0040-93	3-24-93	-	DAP
G1		REVISED PER ECO-17-008808	12MAR2018	RS	DR



AMP WIRE RANGE	E13288 Listed
6 AWG SOLID OR STRANDED	6 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
6 AWG SOLID OR STRANDED	MS20659-143 CLASS 2 P/N 320344 ONLY

- 1 STAMP AMP 6* APPROX AS SHOWN
- 2 UL 486 A-B OR SAE AS7928



100	LOOSE PIECE	320344
QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 10.5-16.8mm²[20,800-33,100] CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± 0.127[.005]
	4 PLC ± -
	ANGLES ± -
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545

DWN TA BRINKMAN 3-24-93	NAME	100	LOOSE PIECE	320344
CHK DA PATTERSON 3-24-93	TERMINAL, RING TONGUE, SOLISTRAND™ 6 AWG	QUANTITY	PACKAGE TYPE	PART NO
APVD JL MECKLEY 3-24-93	TE Connectivity Ltd.	SIZE	CAGE CODE	DRAWING NO
PRODUCT SPEC	RESTRICTED TO	A2	00779	C=320344
APPLICATION SPEC		SCALE	SHEET	REV
WEIGHT		4:1	1 of 1	G1
CUSTOMER DRAWING				