


| ITEM | PART# | DESCRIPTION | QTY | UOM |
|------|-----------|------------------------------------|-----|-----|
| A,B | 430251000 | MicroFit 3.0 DR Rcpt 10Ckt | 2 | PC |
| C | 430300038 | MicroFit 3.0 F Crp Term Chn Tin 18 | 20 | PC |
| D | -- | PAPER PRINTED PAPER WHITE | 1 | PC |

| FROM | TO | DESCRIPTION | COLOR |
|------|-----|-----------------------------------|-------|
| A1 | B5 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A2 | B4 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A3 | B3 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A4 | B2 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A5 | B1 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A6 | B10 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A7 | B9 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A8 | B8 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A9 | B7 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |
| A10 | B6 | 1X18AWG DISC PVC BK UL1061 HOOKUP | BLACK |



| TABLE | | | |
|-------------|--------|--------|--------------------------------------|
| PART NUMBER | L1 | L2 | TITLE |
| 2147551101 | 150±8 | 63REF | MICRO-FIT3.0 R-R 10 CIRCUIT 150MM Sn |
| 2147551102 | 300±10 | 138REF | MICRO-FIT3.0 R-R 10 CIRCUIT 300MM Sn |
| 2147551103 | 600±10 | 287REF | MICRO-FIT3.0 R-R 10 CIRCUIT 600MM Sn |

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

| REVISION | | | |
|------------|-----|-----------------|---------|
| DATE | REV | DESCRIPTION | CHANGER |
| 27/12/2019 | A | INITIAL RELEASE | ARAJU |

| | | | | | | | | | | | | |
|---|---|--|--|------------------|------------------------------|--|----------------------------|--------------------------------------|------------------------|-----------------|--------------------------|---------------|
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | | | | | | | |
| SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 | DIMENSION UNITS: mm SCALE: NTS | | CURRENT REV DESC: EC NO: 629791 DRWN: ARAJU 2019/12/27 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18 | | | | | SEE TABLE | | | | |
| | GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° | | INITIAL REVISION: DRWN: ARAJU 2019/12/27 APPR: RDESAI01 2020/01/18 | | | | | | | | PRODUCT CUSTOMER DRAWING | |
| | 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ± | | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | | | | DOCUMENT NUMBER 2147551100 | | DOC TYPE PSD | DOC PART 000 | REVISION A |
| | THIRD ANGLE PROJECTION | | DRAWING A4-SIZE | SERIES 214755 | MATERIAL NUMBER SEE TABLE | | CUSTOMER GENERAL MARKET | | SHEET NUMBER 1 OF 1 | | | |