



Chat now [Amphenol Sine Systems, USA](#)
[Amphenol Tüchel Industrial, GmbH](#)
[Amphenol Audio, USA](#)



(<https://www.amphenol-sine.com>)

QUICKLY FIND WHAT YOU ARE LOOKING FOR USING OUR PRODUCT SELECTOR

PRODUCT TYPE	NUMBER OF POSITIONS	IP RATING	AMPERAGE	MATERIAL
Search All	Search All	Search All	Search All	Search All
PRODUCT LINE	MAX VOLTAGE	APPLICATION		
Search All	Search All	Search All	RESET SEARCH	

Home (/) > Our Product Lines (/our-product-lines) > A Series (/a-series-connectors) > DuraMate Series (/duramate) > DuraMate AHDP (/duramate-ahdp) > Duramate AHDP 24-19 (/duramate-ahdp-24-19) > AHDP06-24-19SR-BRA 19 Positions, Plug, Socket, Shell Size 24, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-24-19SE-L017 (https://www.amphenol-sine.com/AHDP06-24-19SR-BRA-19-Positions-Plug-Socket-Shell-Size-24-Standard-Arrangement-Reduced-Diameter-Seal-Backshell-Ring-Adapter-Snap-on-Comparable-to-PN-HDP26-24-19SE-L017_p_12514.html)



Click to expand

(<assets/images/AHDP06-24-19SR-BRA.jpg>)

AHDP06-24-19SR-BRA 19 Positions, Plug, Socket, Shell Size 24, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-24-19SE-L017




(<assets/images/AHDP06-24-19SR-BRA.jpg>)

(assets/images/AHDP06-24-19SR-BRA_2.jpg)

-
-

AHDP06-24-19SR-BRA 19 POSITIONS, PLUG, SOCKET, SHELL SIZE 24, STANDARD ARRANGEMENT, REDUCED DIAMETER SEAL, BACKSHELL RING ADAPTER (SNAP -ON). COMPARABLE TO PN# HDP26-24-19SE-L017

PART NUMBER: AHDP06-24-19SR-BRA

DATASHEET:  [View / Download \(pdf/datasheet/AHDP06-24-19SR-BRA.pdf\)](#)

SPECIFICATIONS:

- **Shell Size:** 24
- **No. of positions:** 19
- **Contact Size(s):** 12,16
- **Contact Type (Pin/Socket):** Socket
- **Contacts Included?:** No
- **Gender:** Female (Standard)
- **Wire Range:** 10-14 AWG (6.0-2.0mm²), 14-20 AWG (2.0-0.5mm²)
- **Amperage:** 25,13
- **Housing Material:** Thermoplastic
- **Voltage:** 250 V
- **Operating Temperature:** -55°C to +125°C
- **Color:** Black
- **IP Rating:** IP68 (1M of water for a period of 24 hours, in mated condition)IP69K (in mated condition)
- **Seal Material:** Silicone Rubber
- **Seal Diameter:** 2.46mm (.097") - 4.01mm (.158") / 1.35mm (.053") - 3.05mm (.120")
- **Seal Color:** Blue
- **Rear Seal Type:** Reduced diameter seal
- **Dielectric Value:** Dielectric withstanding voltage less than 2 milliamps current leakage @ 1500 volts AC
- **Insulation Resistance:** 1000 Megaohm min @ 25°C
- **RoHS Compliant?:** Yes
- **Mating Cycle Durability:** >100
- **Mating Part*:** AHDP04-24-19P* & AHDP02-24-19P*

QUANTITY

1	+	 REQUEST A QUOTE
	-	

Like [Sign Up](#) to see what your friends like.

- Description

Description

AHDP06-24-19SR-BRA 19 Positions, Plug, Socket, Shell Size 24, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-24-19SE-L017

RELATED ITEMS