



Chat now [Amphenol Sine Systems, USA](#)
[Amphenol Tuchel Industrial, GmbH](#)
[Amphenol Audio, USA](#)



(<https://www.amphenol-sine.com>)

QUICKLY FIND WHAT YOU ARE LOOKING FOR USING OUR PRODUCT SELECTOR

PRODUCT TYPE Search All	NUMBER OF POSITIONS Search All	IP RATING Search All	AMPERAGE Search All	MATERIAL Search All
PRODUCT LINE Search All	MAX VOLTAGE Search All	APPLICATION Search All	RESET SEARCH	

Home (/) > Our Product Lines (/our-product-lines) > A Series (/a-series-connectors) > DuraMate Series (/duramate) > DuraMate AHDP (/duramate-ahdp) > Duramate AHDP 18-14 (/duramate-ahdp-18-14) > AHDP06-18-14SN-BRA 14 Positions, Plug, Socket, Shell Size 18, Standard Arrangement, Normal Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-18-14SN-L017 (https://www.amphenol-sine.com/AHDP06-18-14SN-BRA-14-Positions-Plug-Socket-Shell-Size-18-Standard-Arrangement-Normal-Diameter-Seal-Backshell-Ring-Adapter-Snap-on-Comparable-to-PN-HDP26-18-14SN-L017_p_12458.html)



Click to expand

([assets/images/AHDP06-18-14SN-BRA.jpg](#))

AHDP06-18-14SN-BRA 14 Positions, Plug, Socket, Shell Size 18, Standard Arrangement, Normal Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-18-14SN-L017



([assets/images/AHDP06-18-14SN-BRA.jpg](#))

([assets/images/AHDP06-18-14SN-BRA_2.jpg](#))

-
-

AHDP06-18-14SN-BRA 14 POSITIONS, PLUG, SOCKET, SHELL SIZE 18, STANDARD ARRANGEMENT, NORMAL DIAMETER SEAL, BACKSHELL RING ADAPTER (SNAP -ON). COMPARABLE TO PN# HDP26-18-14SN-L017

PART NUMBER: AHDP06-18-14SN-BRA

DATASHEET:  [View / Download \(pdf/datasheet/AHDP06-18-14SN-BRA.pdf\)](#)

SPECIFICATIONS:

- **Shell Size:** 18
- **No. of positions:** 14
- **Contact Size(s):** 16
- **Contact Type (Pin/Socket):** Socket
- **Contacts Included?:** No
- **Gender:** Female (Standard)
- **Wire Range:** 14-20 AWG (2.0-0.5mm²)
- **Amperage:** 13
- **Housing Material:** Thermoplastic
- **Voltage:** 250 V
- **Operating Temperature:** -55°C to +125°C
- **Color:** Black
- **IP Rating:** IP68 (1M of water for a period of 24 hours, in mated condition)IP69K (in mated condition)
- **Seal Material:** Silicone Rubber
- **Seal Diameter:** 2.54mm (.100") - 3.40mm (.134")
- **Seal Color:** Green
- **Rear Seal Type:** Normal
- **Dielectric Value:** Dielectric withstanding voltage less than 2 milliamps current leakage @1500 volts AC
- **Insulation Resistance:** 1000 Megaohm min @ 25°C
- **RoHS Compliant?:** Yes
- **Mating Cycle Durability:** >100
- **Mating Part*:** AHDP04-18-14P* & AHDP02-18-14P*

QUANTITY

1	+	 REQUEST A QUOTE
	-	

Like [Sign Up](#) to see what your friends like.

- Description

Description

AHDP06-18-14SN-BRA 14 Positions, Plug, Socket, Shell Size 18, Standard Arrangement, Normal Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-18-14SN-L017

RELATED ITEMS