

CUSTOMER PRINT


PART NUMBER: CA6A808PPXXX90

NOTES:

1. FINISHED PRODUCT TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	"X" DIM
CA6A808PP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CA6A808PP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CA6A808PP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CA6A808PP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CA6A808PPXXX90	



CABLE LENGTH IN "INCHES"



END "A"
FACE VIEW

O-RING
MAT'L: SILICONE, RED

STRAIGHT OVERMOLDED
CABLE CONNECTOR, MALE
MAT'L: UV PBT, BLACK
(2) #16 PIN CONTACTS
(6) #26 PIN CONTACTS
MAT'L: GOLD PLATED COPPER ALLOY



CABLE
(2) 16 AWG CONDUCTORS
(6) 26 AWG CONDUCTORS
JACKET: PRESSED PVC, BLACK
Ø .270 O.D. NOM.
300 VOLTS

COUPLING RING
MAT'L: UV PBT, BLACK
SPRING
MAT'L: STAINLESS STEEL

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS UNLESS INDICATED

WIRE COLOR CODE							
POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6	POS. 7	POS. 8
BLK	WHT	BRN	RED	YEL	GRN	GRY	BLU
16 AWG	16 AWG	26 AWG	26 AWG	26 AWG	26 AWG	26 AWG	26 AWG

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	08-12-21	DRAWING CREATED PER DOR 21-109361DS-1	
REV.	INIT.	DATE	DESCRIPTION	
	MA	08-12-21	<small>ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.</small>	
<small>ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.</small>				
<small>601 E. WILDWOOD VILLA PARK, IL 60181</small>			TITLE: CABLE ASSEMBLY 2#16/6#26 PIN CONTACTS INSTA-CLICK™ MINI-CON-X MIX SIG BULLET CUSTOMER: STANDARD PRODUCT	
SCALE	SIZE	SHEET	PART NUMBER: CA6A808PPXXX90	
NTS	B	1 OF 1	REV A	
FILE:	DIRECTORY:	PART NUMBER: CA6A808PPXXX90		
CA6A808PPXXX90	SLW			