



12		11		10		9		8		7		6		5		4		3		2		1	
0.50mm CENTER FLAT FLEX CABLE (FFC) (105°C, Sn PLATED)																							
"L" DIM. →	30 ± 2 MM		51 ± 2 MM		76 ± 3 MM		102 ± 3 MM		127 ± 4 MM		152 ± 4 MM		178 ± 4 MM		203 ± 4 MM		229 ± 5 MM		254 ± 5 MM		305 ± 5 MM		
REF DIM →	(1.18 INCH)		(2 INCHES)		(3 INCHES)		(4 INCHES)		(5 INCHES)		(6 INCHES)		(7 INCHES)		(8 INCHES)		(9 INCHES)		(10 INCHES)		(12 INCHES)		
CABLE TYPE → CIRCUITS ↓	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	
7	982660745	982660744	982660747	982660746	982660749	982660748	982660751	982660750	982660753	982660752	982660755	982660754	982660757	982660756	982660759	982660758	982660761	982660760	982660763	982660762	982660765	982660764	
9	982660767	982660766	982660769	982660768	982660771	982660770	982660773	982660772	982660775	982660774	982660777	982660776	982660779	982660778	982660781	982660780	982660783	982660782	982660785	982660784	982660787	982660786	
11	982660789	982660788	982660791	982660790	982660793	982660792	982660795	982660794	982660797	982660796	982660799	982660798	982660801	982660800	982660803	982660802	982660805	982660804	982660807	982660806	982660809	982660808	
13	982660811	982660810	982660813	982660812	982660815	982660814	982660817	982660816	982660819	982660818	982660821	982660820	982660823	982660822	982660825	982660824	982660827	982660826	982660829	982660828	982660831	982660830	
15	982660833	982660832	982660835	982660834	982660837	982660836	982660839	982660838	982660841	982660840	982660843	982660842	982660845	982660844	982660847	982660846	982660849	982660848	982660851	982660850	982660853	982660852	
17	982660855	982660854	982660857	982660856	982660859	982660858	982660861	982660860	982660863	982660862	982660865	982660864	982660867	982660866	982660869	982660868	982660871	982660870	982660873	982660872	982660875	982660874	
19	982660877	982660876	982660879	982660878	982660881	982660880	982660883	982660882	982660885	982660884	982660887	982660886	982660889	982660888	982660891	982660890	982660893	982660892	982660895	982660894	982660897	982660896	
21	982660899	982660898	982660901	982660900	982660903	982660902	982660905	982660904	982660907	982660906	982660909	982660908	982660911	982660910	982660913	982660912	982660915	982660914	982660917	982660916	982660919	982660918	
23	982660921	982660920	982660923	982660922	982660925	982660924	982660927	982660926	982660929	982660928	982660931	982660930	982660933	982660932	982660935	982660934	982660937	982660936	982660939	982660938	982660941	982660940	
25	982660943	982660942	982660945	982660944	982660947	982660946	982660949	982660948	982660951	982660950	982660953	982660952	982660955	982660954	982660957	982660956	982660959	982660958	982660961	982660960	982660963	982660962	
27	982660965	982660964	982660967	982660966	982660969	982660968	982660971	982660970	982660973	982660972	982660975	982660974	982660977	982660976	982660979	982660978	982660981	982660980	982660983	982660982	982660985	982660984	
29	982660987	982660986	982660989	982660988	982660991	982660990	982660993	982660992	982660995	982660994	982660997	982660996	982660999	982660998	982661001	982661000	982661003	982661002	982661005	982661004	982661007	982661006	
31	982661009	982661008	982661011	982661010	982661013	982661012	982661015	982661014	982661017	982661016	982661019	982661018	982661021	982661020	982661023	982661022	982661025	982661024	982661027	982661026	982661029	982661028	
33	982661031	982661030	982661033	982661032	982661035	982661034	982661037	982661036	982661039	982661038	982661041	982661040	982661043	982661042	982661045	982661044	982661047	982661046	982661049	982661048	982661051	982661050	
35	982661053	982661052	982661055	982661054	982661057	982661056	982661059	982661058	982661061	982661060	982661063	982661062	982661065	982661064	982661067	982661066	982661069	982661068	982661071	982661070	982661073	982661072	
37	982661075	982661074	982661077	982661076	982661079	982661078	982661081	982661080	982661083	982661082	982661085	982661084	982661087	982661086	982661089	982661088	982661091	982661090	982661093	982661092	982661095	982661094	
39	982661097	982661096	982661099	982661098	982661101	982661100	982661103	982661102	982661105	982661104	982661107	982661106	982661109	982661108	982661111	982661110	982661113	982661112	982661115	982661114	982661117	982661116	
41	982661119	982661118	982661121	982661120	982661123	982661122	982661125	982661124	982661127	982661126	982661129	982661128	982661131	982661130	982661133	982661132	982661135	982661134	982661137	982661136	982661139	982661138	
43	982661141	982661140	982661143	982661142	982661145	982661144	982661147	982661146	982661149	982661148	982661151	982661150	982661153	982661152	982661155	982661154	982661157	982661156	982661159	982661158	982661161	982661160	
45	982661163	982661162	982661165	982661164	982661167	982661166	982661169	982661168	982661171	982661170	982661173	982661172	982661175	982661174	982661177	982661176	982661179	982661178	982661181	982661180	982661183	982661182	
47	982661185	982661184	982661187	982661186	982661189	982661188	982661191	982661190	982661193	982661192	982661195	982661194	982661197	982661196	982661199	982661198	982661201	982661200	982661203	982661202	982661205	982661204	
49	982661207	982661206	982661209	982661208	982661211	982661210	982661213	982661212	982661215	982661214	982661217	982661216	982661219	982661218	982661221	982661220	982661223	982661222	982661225	982661224	982661227	982661226	



CROSS-SECTION



END TAIL DETAIL
SCALE 10:1

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC: DRAWING CORRECTION				molex 0.50MM CENTER FLAT FLEX CABLE (FFC) (105°C, SN PLATED) SALES DRAWING						
MM		NA												
GENERAL TOLERANCES (UNLESS SPECIFIED)														
		mm	INCH	EC NO: 728054										
4 PLACES	±----	±----	±----	DRWN: DIEGOG72022/11/10										
3 PLACES	±----	±----	±----	CHK'D: JSMITH112022/11/14										
2 PLACES	±----	±----	±----	APPR: JSMITH112022/11/14										
1 PLACE	±----	±----	±----	INITIAL REVISION:										
0 PLACES	±----	±----	±----	DRWN: DIEGOG72022/09/22										
ANGULAR TOL ± 0.5 °				APPR: JSMITH112022/11/03										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER			
						C-SIZE	98266	SEE CHART	GENERAL MARKET		2 OF 2			

DOCUMENT STATUS	P1	RELEASE DATE	2022/11/14	14:34:31
-----------------	----	--------------	------------	----------