










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



- NOTES:
- MATERIAL:
HOUSING: PBT UL94V-0.
PIN: COPPER ALLOY
 - MATING PARTS:
PLUG HOUSING: X-2420266-X,
SOCKET CONTACT: X-2420268-X.

 TRADE MARK : TE

CIRCUITS	COLOUR	KEYING	P/N	DIMENSIONS(mm)		
				A	B	C
6(2*3)	Light blue	/	2423324-6	12.7	8.0	7.4
8(2*4)	Light blue	/	2423324-8	16.7	12.0	9.4
10(2*5)	Light blue	/	1-2423324-0	20.7	16.0	8.8
12(2*6)	Light blue	/	1-2423324-2	24.7	20.0	8.8
14(2*7)	Light blue	/	1-2423324-4	28.7	24.0	8.8



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JI 10JUN2022		 TE Connectivity Ltd.																	
		CHK NIKI SHI 10JUN2022																			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HCI 4.0 PITCH WTB HEADER — —																	
		APVD NIKI SHI 10JUN2022																			
		PRODUCT SPEC																			
		—																			
		APPLICATION SPEC																			
		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO											
MATERIAL		FINISH		WEIGHT		A2		00779		C=2423324		—									
				CUSTOMER DRAWING						SCALE		N.T.S		SHEET		2 of 5		REV		A1	

4

3

2

1

© 2022TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

TYPE A

2P

3P

4P

5P

TYPE B

3P

4P

5P

TYPE C

3P

4P

5P

6P

8P

10P

12P

14P

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES, UNLESS OTHERWISE SPECIFIED:
0 PLC ± —
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH
—

DWN
JONE_JI
10JUN2022

CHK
NIKI_SHI
10JUN2022

APVD
NIKI_SHI
10JUN2022

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity Ltd.

NAME
HCI 4.0 PITCH WTB HEADER
—
—

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2423324

RESTRICTED TO
—

SCALE
N.T.S

SHEET
3 OF 5

REV
A1

1471-9 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




FIGURE 1





FIGURE 2





FIGURE 3





FIGURE 4





FIGURE 5





FIGURE 6


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JI 10JUN2022	TE Connectivity Ltd.		
		CHK NIKI SHI 10JUN2022			
		APVD NIKI SHI 10JUN2022	NAME HCI 4.0 PITCH WTB HEADER		
		PRODUCT SPEC 108-160771			
		APPLICATION SPEC 114-160464			
		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=2423324
		CUSTOMER DRAWING	SCALE N.T.S	SHEET 4 OF 5	REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE LIST

TE P/N	PE BAG	Q' TY	Q' TY/BOX
X-2423324-2	400 PCS	2000 PCS	8000 PCS
X-2423324-3	300 PCS	1500 PCS	6000 PCS
X-2423324-4	200 PCS	1000 PCS	4000 PCS
X-2423324-5	200 PCS	1000 PCS	4000 PCS
X-2423324-6	200 PCS	1000 PCS	4000 PCS
X-2423324-8	200 PCS	1000 PCS	4000 PCS
1-2423324-0	150 PCS	750 PCS	3000 PCS
1-2423324-2	100 PCS	500 PCS	2000 PCS
1-2423324-4	100 PCS	500 PCS	2000 PCS

2423324

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JI 10JUN2022	 TE Connectivity Ltd.			
		CHK NIKI SHI 10JUN2022				
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.30 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		NAME HCI 4.0 PITCH WTB HEADER		
		APVD NIKI SHI 10JUN2022		PRODUCT SPEC 108-160771		
		APPLICATION SPEC 114-160464		SIZE A2		
MATERIAL -		WEIGHT -		CAGE CODE 00779	DRAWING NO C=2423324	RESTRICTED TO -
CUSTOMER DRAWING				SCALE N.T.S	SHEET 5 OF 5	REV A1