

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


53324-0660

Status:

Active

Description:

2.00mm Pitch Mi II™ System Wire-to-Board Header, Single Row, Vertical, Lead-Free, 6 Circuits



Documents:	
3D Model	Product Specification PS-52484-021 (PDF)
Drawing (PDF)	Packaging Specification SPK-53324-001 (PDF)
Product Specification PS-51090-016 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	53324
Application	Signal, Wire-to-Board
Product Name	Mi II™
UPC	756054680971
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	376.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

53324Series

Mates With

52484 Wire-to-Board IDT Receptacle, 51090 Crimp Terminal

Current - Maximum per Contact2A

Voltage - Maximum125V

Material Info

Reference - Drawing Numbers

Packaging SpecificationSPK-53324-001

Product SpecificationPS-51090-016, PS-52484-021, RPS-51090-001,
RPS-51090-017, RPS-51090-022, RPS-52484-022,
RPS-52484-025, RPS-52484-026, RPS-53324-001

Sales DrawingSD-53324-003

This document was generated on 10/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION