

166-90221

HellermannTyton



Article Number: 166-90221

Description: HelaGuard SR PVC Tubing, Smooth Bore, Spiral Cover, Std Wt, 0.50" Dia, Bk, 100 ft/Std. Reel

Base Data		
	Local Order Number	166-90221
	Type	PSR0500
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Spiral reinforced construction provides protection from crushing yet remains extremely flexible. • Lightweight, easy-to-use material reduces installation time and labor costs. • Material stands up to vibration and limited torsional movement without creation of stress points or cracks. • Smooth inside bore protects wires and eases insertion of wire bundles. • UV resistant; suitable for use in outdoor applications.
	Quantity Per	reel
	Product Description	A lightweight tubing with a smooth inside bore, made of a spiral reinforced PVC material that provides high flexibility. This tubing is well-suited for protecting wire and cable bundles in extremely tight spaces. UV resistant. Use with HelaGuard Non-Metallic Compression Fittings to create an enclosed system.
	Short Description	HelaGuard SR PVC Tubing, Smooth Bore, Spiral Cover, Std Wt, 0.50" Dia, Bk, 100 ft/Std. Reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.5m
	Inner Diameter D (Imperial)	0.63"
	Inner Diameter D (metric)	16mm
	Trade Size	1/2 "
	Outside Diameter D (imperial)	0.83"
	Outside Diameter D (metric)	21.0mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	20mm
	Inside Bend Radius (Imperial)	1.38"
	Inside Bend Radius (Metric)	35mm

166-90221



Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Flammability	self-extinguishing according to EN IEC 61386
	Halogenfree	No
	Operating Temperature	-4°F to +158°F (-20°C to +70°C)
	ROHS Compliant	Yes
	UL Recognized (US)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.5m
	Customs Number(Schedule B)	3926909987