



PRODUCT DESCRIPTION

The M1380 is a complete audio solution for an array of audio applications. The 2.1 speaker system features two full range satellites tuned, calibrated and matched with the subwoofer to form a balance of clarity, richness and full audio output. Equipped with a wired remote that includes a headphone jack and an auxiliary 3.5mm stereo input on the unit, the M1380 can be used solo or easily connected to any host device.

FEATURES

- Wooden MDF enclosed subwoofer with front bass reflex port that delivers rich and detailed audio.
- Two full-range satellites tuned, calibrated and matched with the subwoofer
- Auxiliary 3.5mm stereo input
- Wired remote controller with headphones jack

SPECIFICATIONS

Total power output:	RMS 8W x 2 + 12W x 1
THD + N (testing level):	10%
Signal to noise ratio:	≥85dBA
Distortion:	≤0.5%
Input sensitivity:	Satellites: 450mV ± 50mV Subwoofer: 70mV ± 20mV
Input impedance:	10KΩ
Frequency response:	R/L: 140Hz - 20KHz SW: 20Hz - 130Hz
Audio input type:	3.5mm Stereo line-in, Auxiliary input, Headphone jack
Adjustment:	Power, Base, Volume, Mute
Subwoofer / bass unit:	5 inch (131mm), 4Ω
Tweeter unit:	2¼ inch (70mm), 4Ω
Remote control:	Wired: Volume control, headphone jack, mute
Control panel:	Bass trimmer, Power switch
Dimension:	Satellites: 120mm × 151mm × 125mm Subwoofer: 164mm × 220mm × 280mm (WxHxD)
Weight:	≈4.20Kg (net) / ≈5.20Kg (gross)

ORDERING DETAILS

EAN: 6923520262397	Model no.: M1380	Description: 2.1 Multimedia speakers
------------------------------	----------------------------	--

*All specifications are subject to change without notice.

a passion for sound®