# **PCB TERMINAL BLOCKS**

# 5.08mm DIN Rail Mounted Inverted/Reverse

- · Horizontal & vertical orientations
- Polarized moldings
- · Can be reversed on DIN clips
- · Also available in 5mm pitch
- Molded in green UL94-V0 flame retardant PA 66
- 2.5mm2 (28-14AWG)
- calus approved
- · 6-12 poles standard (13-24 also available)

SPECIFICATION	
Rating	UL=15A/300V IEC 20A/450V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Brass, Tin plated
Rising Clamp	Brass, nickel plated
Screw/Torque	M3 Steel, zinc plated 0.5Nm


## **DIN Rail Male Vertical Connector**


TYPE NO.	POLES	LENGTH
CTBPD96VJ/6	6	32.0mm
CTBPD96VJ/7	7	37.1mm
CTBPD96VJ/8	8	42.2mm
CTBPD96VJ/9	9	47.2mm
CTBPD96VJ/10	10	52.3mm
CTBPD96VJ/11	11	57.4mm
CTBPD96VJ/12	12	62.5mm


#### CTBPD96VJ



Excludes DIN Rail









### **DIN Rail Male Vertical Connector, Flanged**

TYPE NO.	POLES	LENGTH A	LENGTH B
CTBPD96VJ/6FL	6	32.0mm	41.8mm
CTBPD96VJ/7FL	7	37.1mm	46.9mm
CTBPD96VJ/8FL	8	42.2mm	52.0mm
CTBPD96VJ/9FL	9	47.2mm	57.0mm
CTBPD96VJ/10FL	10	52.3mm	62.1mm
CTBPD96VJ/11FL	11	57.4mm	67.2mm
CTBPD96VJ/12FL	12	62.5mm	72.3mm

#### CTBPD96VJ/FL







PCB TERMINAL BLOCKS

INTER-CONNECTION

> FUSES & FUSE-HOLDERS

LEDs & INDICATORS

MINIATURE SWITCHES

LIMIT & SAFETY SWITCHES

CONTROL PRODUCTS

INTERFACE MODULES & SUPPORTS

> RELAY BASES

DIN RAIL ENCLOSURES

BATTERIES

SOLAR PANELS

TRANS-FORMERS