



Ready when you are

M VESA Flexarm Full Motion Dual 400x400

Article: 7 350 073 735 266

M VESA Flexarm Full Motion Dual, 400x400 - Wall mount for LCD / plasma panel - screen size: 40" - 70"

Product category: WALLMOUNTS



Specification

M VESA Flexarm Full Motion Dual, 400x400

For screen size:	40-70"
Tilt:	-2° ~ +10°
Turn:	Up to -45° ~ +45°, screen size dependant
VESA standard:	100x100 200x100 200x200 300x300 300x200 400x200 400x400
Article No:	7 350 073 735 266
Size in mm:	595*294*46-488 (W*H*D)
Distance to wall:	46mm
Weight:	8 kg
Colour:	Black
Max load:	45 kg
Distribution package:	2 pcs
Warranty:	5 years
Retail box size (WxDxH):	600 x 430 x 650 mm
Units on a EUR-pallet:	64 pcs

Retail Package Specification

Package Parcels:	1 pcs
Package Measurements:	0 x 0 x 0 cm
Package Weight:	0.00 kg

Distribution Package Specification

Retail Package Parcels:	4 pcs
Package Measurements:	0 x 0 x 0 cm
Package Weight:	0.00 kg

The content of this specification is subject to change without further notice. Always visit our web for the latest updated specifications. <https://products.multibrackets.com/>