



Ready when you are.



M Motorized Swing Mount Large

Art No: 7 350 022 734 500

The M Motorized Swing Mount is a swing mount type motorized arm. It makes your wall mounted TV swing around a corner 90 degrees either left or right. This allows you to watch your TV from anywhere, whether it is living room or kitchen.

Multibrackets Motorized Swing Mount fits nearly all TVs, requires no additional peripherals to be installed

(all included) and it is easy to install, and then easy to operate with your own TV remote.

The M Motorized Swing Mount optimizes your TV visibility and as the TV can be mounted so that either left or right swing is possible, you do not need to double-check which way your TV is going to swing out before a purchase.

SPECIFICATIONS

M Motorized Swing Mount Large	
For screen size:	37-55"
VESA standard:	200x200 300x200 300x300 400x200 400x400 600x400 mm
EAN:	7 350 022 734 500
Colour:	Black
Max load:	30 kg
Recommended maxload per screen size:	55" 22Kg
	46" 25Kg
	42" 30Kg
Distribution package:	2 pcs
Warranty:	1 year
Remote control:	Any IR remote control (IR Standard RC5)
Certification:	CE, TUV
Power:	DC12V, 0,5A
Distance to wall:	52,3 mm
Swing range:	0-90 degrees; left or right
Weight:	10,8 kg
Size in mm:	296x897x53 (WxLxH)
Gift box size in mm:	365x960x120 (WxLxH)

