

Part Number:0875682093

Status:Active

Overview:Milli-Grid Connector System

Description:Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

Documents:

3Dモデル

梱包仕様書 PK-87568-0001-001 (PDF)

図面 (PDF)

RoHS Certificate of Compliance (PDF)

製品仕様書 PS-87568-004-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

一般

Crimp Quality Equipment

概要

製品名

UPC

適合相手

有

Milli-Grid Connector System

Milli-Grid

822348457755

87569-1020

Strain Relief (Optional)

機械的性能/材質

極数 (実装)

極数 (最大)

色 - 樹脂部

耐久挿抜回数

難燃性

ジェンダー

Glow-Wire Capable

嵌合ロック

材質 - 金属部

材質 - 嵌合部メッキ

材質 - 樹脂部

Net Weight

列数

梱包形態

パネルマウント

ピッチ - 嵌合部 (インチ)

嵌合極性

縦列スタック (エンド・ツー・エンド)

使用温度範囲

実装スタイル

電線サイズ (AWG)

20

20

黒色

100

94V-0

フィメール

無

有

銅合金

金

Polyester

1.241/g

2

トレー

無

2.00mm

有

無

-20° to +85° C

圧接または貫通

28

電気的性能

最大定格電流

最大定格電圧

1.0A

125V

Solder Process Data

Lead-freeProcess Capability

N/A

参考情報

図面・仕様書情報

梱包仕様書

製品仕様書

PK-87568-0001-001

PS-87568-004-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/61/2018 (27 June

2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87568 Series

Mates With

87831 Vertical PCB Header, 87832

Surface Mount PCB Header, 87833 Right

Angle PCB Header

This document was generated on 10/01/2018  
PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION