


[About Us](#)
[Product](#)
[Contact Us](#)
[Support / Download](#)
[Where to Buy](#)
 QUICK446

[Home](#) » [Search](#) » [Ionizing Air Gun/High Voltage Power Supply QUICK445D QUICK446](#)

Categories

[Robot Series \(9\)](#)
[BGA Rework System \(1\)](#)
[Fume Extractor \(2\)](#)
[Soldering Equipment Series \(11\)](#)
[Rework Equipment Series \(11\)](#)
[Static Eliminator & Meter Series \(5\)](#)
[Other Products \(4\)](#)

Ionizing Air Gun/High Voltage Power Supply QUICK445D QUICK446



Product Code: QUICK445D QUICK446

Availability: In Stock

[Add to Compare](#)

☆☆☆☆ 0 reviews [Write a review](#)

[Share](#)

Description	Reviews (0)
-------------	-------------

Features:

- Compact design, easy operation.
- Neutralize static charges rapidly, remove fine sensitive components and materials easier.
- Built-in regulator of remnant voltage, adjust ion balance quickly and effectively.
- Two ionizing air guns can be connected to QUICK446 high-voltage power supply at the same time.
- Purchase separately.

Specifications:

Frequency of QUICK446	50Hz/60Hz
Secondary Output Voltage	AC 4.0KV
Power Consumption	20W
Dimensions	165(L)×103(W)×115(H)mm
Weight	3.8Kg

Note:

Ambient conditions: About 0-50°C , 60-70% RH.

Life expectancy: About 10000 hours (based on 8h/d, 250d/y, around 5 years).

Time for Static Neutralizing:

Pressure	Air flow	Decay time	Noise
0.2Mpa	0.06m ³ /min	1.2s	≤71dB
0.4Mpa	0.12 m ³ /min	0.6s	≤88dB
0.6Mpa	0.18 m ³ /min	0.4s	≤95dB
0.7Mpa	0.20 m ³ /min	0.3s	≤98dB

Note:

Testing distance: 15cm from the outlet of the air gun.

