

MKT-A capacitors

Foil Capacitors for professional crossovers, low loss and high power handling. Axial design. DC strength **250 V** (**100 V** for models 82 μF and 100 μF).



Art. No.	Article	Technical Data
5419	MKT-A 1,0 μF	Dimensions (D x L) 8 x 24 mm
5421	MKT-A 1,5 μF	Dimensions (D x L) 9 x 30 mm
5423	MKT-A 2,2 μF	Dimensions (D x L) 10 x 30 mm
5425	MKT-A 3,3 μF	Dimensions (D x L) 14 x 30 mm
5427	MKT-A 4,7 μF	Dimensions (D x L) 17 x 32 mm
5428	MKT-A 5,6 μF	Dimensions (D x L) 17 x 32 mm
5429	MKT-A 6,8 μF	Dimensions (D x L) 16 x 45 mm
5430	MKT-A 8,2 μF	Dimensions (D x L) 16 x 45 mm
5431	MKT-A 10 μF	Dimensions (D x L) 19 x 45 mm
5432	MKT-A 15 μF	Dimensions (D x L) 22 x 45 mm
5433	MKT-A 22 μF	Dimensions (D x L) 27 x 45 mm
5435	MKT-A 33 μF	Dimensions (D x L) 30 x 55 mm
5437	MKT-A 47 μF	Dimensions (D x L) 33,5 x 55 mm
5438	MKT-A 56 μF	Dimensions (D x L) 39 x 55 mm
5439	MKT-A 68 μF	Dimensions (D x L) 41 x 60 mm
5441	MKT-A 82 μF	Dimensions (D x L) 34 x 55 mm
5443	MKT-A 100 μF	Dimensions (D x L) 38 x 56 mm