



Ready when you are

M VESA Flexarm Tilt & Turn II

Article: 7 350 022 734 210

Multibrackets M VESA Flexarm Tilt & Turn II - Wall mount for LCD / LED panel - black - screen size: 32" - 50"

Product category: WALLMOUNTS



Specification

M VESA Flexarm Tilt & Turn II

For screen size:	32-50"
Universal & VESA standard:	100x100 200x100 200x200 300x300 300x200 400x200 400x400
Article No:	7 350 022 734 210
Size in mm:	488x273x47 (W*H*D)
Weight:	3,6 kg
Colour:	Black
Max load:	25 kg
Distribution package:	4 pcs
Warranty:	5 years
Cable tie:	Included
Security lock:	Optional
Single box size (WxDxH):	550x78x340mm
Units on a EUR-pallet:	80 pcs

Retail Package Specification

Package Parcels:	1 pcs
Package Measurements:	56 x 36 x 33 cm
Package Weight:	3.60 kg

Distribution Package Specification

Retail Package Parcels:	4 pcs
Package Measurements:	0 x 0 x 0 cm
Package Weight:	0.00 kg

The content of this specification is subject to change without further notice. Always visit our web for the latest updated specifications. <https://products.multibrackets.com/>