



Ready when you are

M VESA Super Slim Tilt & Turn HD

Article: 7 350 022 735 101

Multibrackets M VESA Super Slim Tilt & Turn HD - Wall mount for LCD / LED panel - black - screen size: 40" - 85"

Product category: WALLMOUNTS



Specification

M VESA Super Slim Tilt & Turn HD (Heavy Duty)

For screen size:	40-85"
Universal & VESA standard:	100x100 200x100 200x200 300x300 300x200 400x200 400x400
Article No:	7 350 022 735 101
Size in mm:	595*294*50 (W*H*D)
Distance to wall:	VESA 100 / 200 / 300: 40mm
Distance to wall with extender arms:	VESA 400: 50mm
Weight:	7,7 kg
Colour:	Black
Max load:	52 kg
Distribution package:	4 pcs
Warranty:	5 years
Distance to wall:	min 48mm - max 260mm
Single box size (WxDxH):	687x80x365mm
Units on a EUR-pallet:	80 pcs
For VESA 600x400 600x300 600x200:	Combine with optional M Extender Kit Tilt & Turn

Retail Package Specification

Package Parcels:	1 pcs
Package Measurements:	60 x 38 x 8 cm
Package Weight:	7.50 kg

Distribution Package Specification

Retail Package Parcels:	4 pcs
Package Measurements:	0 x 0 x 0 cm
Package Weight:	0.00 kg

The content of this specification is subject to change without further notice. Always visit our web for the latest

updated specifications. <https://products.multibrackets.com/>