

Description

The Game Max Pulse RGB Gaming keyboard and Mouse is a great combo for all gamers looking to upgrade their current kit without breaking the bank.

The Keyboard is made using rubber dome switches making the keyboard a lot quieter during use. The strong, crisp tactile keys enable complete control during game play and a short travel time makes the response time quicker than ever. The keyboard comes with 13 multimedia functions, 26 anti-ghosting keys and you can swap the cursor keys and WASD keys.

The mouse is an optical 7D gaming mouse equipped with excellent cursor accuracy, clutch the victory with pixel-point perfection and 6 DPI pre-sets means you match the mouse to your style of play.

The kit has a 7 colour RGB backlight, you can sync everything to the same colour mode or you can mix and match to fit in with the rest of your set-up. The colours include Red, Blue, Green, Cyan, White, Purple and Yellow. These are easily changeable at the touch of a button.

The Pulse is compatible for both Windows & Mac OSX. In line with the Game Max ethos this combo offers style, performance and the ultimate experience.

Key Features

- **Gaming Rubber Dome Switches** - The Pulse keyboard comes with rubber dome switches creating minimum noise and a satisfying feel without sacrificing performance.
- **Multi-Key Anti-Ghosting** - 26 anti-ghosting keys makes sure all your commands and keystrokes register the way you intended.
- **Design Of The Gaming Mouse** - The gaming mouse included in the Pulse is a well thought out design, the ergonomic, rubber coated design enables precise positioning and with every button carefully designed and placed to be easily identifiable by touch.
- **Dynamic RGB Backlighting** - The Pulse comes with 7 colours to choose from and several different colour modes, the user has a choice between static and breathing colour lighting modes. The brightness and LED running speed can be easily adjusted.
- **On-The Fly Adjustable DPI** - Ideal for first time and experienced gamers with a 3200dpi optical sensor you can now get the right level of precision and pixel precise targeting for whatever game you are playing.
- **Wrist Rest** - Additional comfort to support your gameplay during those long gaming sessions.
- **Music & Voice Indicators** - Built in voice indicators enables you to get the RGB lighting effects to follow sounds from your gaming environment.
- **Braided Cables** - The USB connectors come with braided cables offering excellent durability and will last a lot longer than a standard cable.

Specifications

Keyboard:

Connectivity: USB

Keyboard Qty: 105 Keys (13 Multimedia Keys + LED Button)

Cable Length: 1.75m

LED Colour: 7 (Red, Blue, Green, Cyan, White, Purple & Yellow)

Working Power: 5V=300mA

M.T.B.F: 5 Million Keystrokes

Multimedia

Functions (From 13

Left To Right):

- 1** : Mute System Volume
- 2**: Decrease System Volume
- 3**: Increase System Volume
- 4**: Play Previous Media Track
- 5**: Stop Current Media Track
- 6**: Open Home Page
- 7**: Open Default E-mail Program (Not Web Mail)
- 8**: Open My Computer
- 9**: Open Calculator
- 10**: Play Previous Media Track
- 11**: Play Next Media Track

12: Open My Favourites

13: Open The Search

Anti Ghosting: 26 Keys

Key Elasticity: 55g ± 7g

Pre-Travel

Distance of Keys 3mm

:

Total Travel

Distance of 5.5mm

Keys:

Working

Environment 0°C to 45°C

Temperature:

Operating 20-90%

Humidity :

Working 5V

Voltage:

Working 300mA (max.)

Current:

Software Windows 2000 / XP / ME / Vista / 7 / 8 / 10 / / Android

Compatibility: / Linux / MAC OSX

Net Weight: 580 ± 20g

Mouse:

Connectivity: USB

Button Qty: 7 Buttons

LED Colour: 7 (Red, Blue, Green, Cyan, White, Purple & Yellow)

Materials: ABS

Cable Length: 1.8m

Resolution: 600 / 800 / 1200 / 1600 / 2400 / 3200 DPI

Button M.T.B.F: 3 Million Keystrokes

Maximum 15G

Acceleration:

Mouse Type: Optical

Mouse Grip: 6000fps

On-Sensor A714F

Code:

Maximum 60 Inch/Second

Tracking Speed:

Polling Rate: 125HZ

Working Power: 5V=100mA

Working 5V

Voltage:

Working 100mA (max.)

Current:

Software Windows 2000 / XP / ME / Vista / 7 / 8 / 10 / Android /

Compatibility: Linux / Mac OSX

Net Weight: 141 ± 10g

General Specifications

Manufacturer GMX-PULSE

Part Number:

EAN Number: 5055492408006

Has Mains Plug: No

Colour: Black

What's In The Keyboard

Box: Mouse

User Manual

Unit (Product)

Dimensions 440mm x 26mm x 165mm (W x H x D)

(mm):

Packaging

Dimensions 530mm x 180mm x 45mm (W x H x D)

(mm):

Net Weight 0.7 KGs

(KGs):

Gross Weight 1 KGs
(KGs):