

Heatshrink Box

Product Type:

Heatshrink Tubing Box Pack



Detail:

- Operating temperature -55°C to +120°C
- Minimum shrink temperature 70°C
- Full recovery temperature: 120°C
- Shrink Ratio 2:1
- RoHS Compliant
- Colour: Black, Red, Blue, Yellow, Green & Yellow

Application:

Manufactured with modified radiation cross-linked polyolefin. The specially designed halogen free formulation makes the tubing very flexible and shrinks at lower temperature. Suitable for applications where temperature sensitive components protection, e.g. PVC jacketed wire and cable and quick shrinkage is required. It has good mechanical and electrical performances.

Code	Description	Box Length
AHSB2.4RED	Heatshrink Box 2:1 2.4mm Red 20m	20m
AHSB3.2RED	Heatshrink Box 2:1 3.2mm Red 20m	20m
AHSB3.2BLU	Heatshrink Box 2:1 3.2mm Blue 20m	20m
AHSB4.8BLU	Heatshrink Box 2:1 4.8mm Blue 10m	10m
AHSB4.8BLK	Heatshrink Box 2:1 4.8mm Black 10m	10m
AHSB6.4BLK	Heatshrink Box 2:1 6.4mm Black 10m	10m
AHSB6.4BLU	Heatshrink Box 2:1 6.4mm Blue 10m	10m
AHSB9.5BLU	Heatshrink Box 2:1 9.5mm Blue 10m	10m
AHSB9.5G/Y	Heatshrink Box 2:1 9.5mm Green/Yellow 10m	10m
AHSB12.7YEL	Heatshrink Box 2:1 12.7mm Yellow 5m	5m
AHSB19.1RED	Heatshrink Box 2:1 19.1mm Red 5m	5m
AHSB19.1BLU	Heatshrink Box 2:1 19.1mm Blue 5m	5m
AHSB19.1BLK	Heatshrink Box 2:1 19.1mm Black 5m	5m
AHSB25.4BLU	Heatshrink Box 2:1 25.4mm Blue 5m	5m
AHSB25.4BLK	Heatshrink Box 2:1 25.4mm Black 5m	5m
AHSB25.4RED	Heatshrink Box 2:1 25.4mm Red 5m	5m
AHSB25.4G/Y	Heatshrink Box 2:1 25.4mm Green/Yellow 5m	5m