



## BEE EFFECT MOVING HEAD 4x10W

### BEE40-LED

Rotating bee effect moving head that scans the premises with bright, dynamic beams. The lens is adjustable to rotate endlessly in 2 directions to create a graphic effect or come together to one single bright beam.

- 4 or 16 DMX channels
- Auto, DMX, master-slave or sound control
- 8 built-in programs, with sound control in DMX mode
- Scan position memory
- 3-color wheel (red, yellow and blue) + open white, rainbow effect
- Narrow beam 5°
- Linear dimmer 0-100%

**EAN CODE** **5420047134769**  
**16-2000**

### SPECIFICATIONS TECHNIQUES

Power supply	100-240Vac 50/60Hz
Consumption	55W
Light source	4x white 10W LED
Pan/Tilt	540°/190° 2 speed levels
Strobe	0-23Hz
Dimensions	245 x 145 x 330mm
Weight	4.06kg



### LOGISTICS VALUES

Height	31 cm
Width	23 cm
Depth	15 cm
Volume	5E-06 m <sup>3</sup>
Net weight	4.53 kg
Packaging height	29 cm
Packaging width	36.5 cm
Packaging depth	30 cm
Packaging volume	0.032 m <sup>3</sup>
Packaging gross weight	5.33 kg
Master carton height	32 cm
m carton largeur	37 cm
m carton profondeur	62 cm
m carton volume	0.073408 m <sup>3</sup>
m carton poids net	11.52 kg
m carton poids brut	11.52 kg
Palette hauteur	0.46 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per shipping box	2
nb uvc par palette	2
nb couches parpalette	1
nb cartons par couche	1
EAN14 code	54200471347692
Customs code	94054091

