



**LIGHT STAND FITTED WITH 2x RGBW PAR CANS
+ 2x RGBWA MOON**

DJLIGHT60

The set contains following items:

- 2 x PAR cans fitted with 12x 1W RGBW LEDs
- 2 x Moon Flower effects with RGBWA LEDs
- Crossbar that powers the PAR cans
- 9/19-channel DMX, master-slave, auto & remote control
- Remote control
- Black stand with anti-slip feet
- Power cable 4m
- Pre-mounted DMX signal cable on all 4x cans

**EAN
CODE**

**5420047130709
15-1185**

SPECIFICATIONS TECHNIQUES

Height	1.80m max.
Weight	5.6kg



LOGISTICS VALUES

Height	90.5 cm
Width	31 cm
Depth	23.5 cm
Volume	6E-06 m ³
Net weight	6 kg
Packaging height	92 cm
Packaging width	38 cm
Packaging depth	18.5 cm
Packaging volume	0.065 m ³
Packaging gross weight	7 kg
Master carton height	92 cm
m carton largeur	38 cm
m carton profondeur	18.5 cm
m carton volume	0.064676 m ³
m carton poids net	7 kg
m carton poids brut	7 kg
Palette hauteur	1.98 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per shipping box	1
nb uvc par palette	24
nb couches parpalette	2
nb cartons par couche	12
Customs code	94054091

