

## S105 / S108

### Delicate Design , Art of Tech Plug and play , easy to expand your wired network

#### 5 / 8 Port Fast Ethernet Switch

Tenda S105/S108 5/8-port 10/100Mbps Ethernet Switch is a desktop switch, which is specially designed for families, offices, dormitories etc. Up to 200Mbps full duplex rate brings blazing fast Internet access. Plug-and-play design makes installation easy. Low power consumption makes you enjoy a healthy e-life. Compatible with computers, printers, smart TVs, NAS, smart game consoles, IP-cameras, Tenda S108 lets you enjoy a freewheeling and fashionable e-life.



#### Plug and Play, Rapid Forwarding

Play the device as long as you plug it, without any configuration. Rapid store-and-forward mechanism guarantees you a fluent and rapid online gaming, HD video and IP camera monitoring experience.

#### Mini and Fashionable Design

The switch, with polished cambered checked white surface, is mini case and pocket design, smaller than your VISA card(S105).

#### Wall & Desktop Mounting Design

Supports wall or desktop mounting. The wall-mounting guarantees a stable and firm network cabling when you deploy a network outdoor/indoor, like IP camera monitoring.

#### Green and Energy-saving

Lower consumption. The max power consumption of S105 is 1.6W, and that of S108 is 2.15W. It is low-carbon and energy-saving.

## Specifications

		S105	S108
Hardware Features	Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3x	
	Interface	5*10/100M auto-negotiation RJ45 ports (Auto MDI/MDIX)	8*10/100M auto-negotiation RJ45 ports (Auto MDI/MDIX)
	Transmission Media	10Base-T: Cat. 3 UTP or better 100Base-TX: Cat.5 UTP	
	Forwarding Speed	10Mbps: 14880pps 100Mbps: 148800pps	
	Power Supply	Input: AC:100-240V; 50/60Hz Output: 5.0V 0.6A ( External Power Adapter )	
	Product Dimensions ( L*W*H )	82.00mm*52.00mm*22.30mm	124.00mm*59mm*23.1mm
	LEDs	1* Power, 5* Link/Act	1* Power, 8* Link/Act
	Switching Capacity	1.0Gbps	1.6Gbps
	MAC Address Table	1K	
	Power Consumption	Maximum : 1.60W (220V)	Maximum : 2.15W (220V)
Software Features	Transfer Method	Store and Forward	
	Access Control	CDMA/CD	
	MAC Address Learning	Automatic update	
Others	Temperature	Operating Temperature: 0°C~40°C Storage Temperature: -40°C~70°C	
	Humidity	Operating Humidity: 10%~90% non-condensing Storage Humidity: 5%~90% non-condensing	
	Certification	CE , FCC , RoHS , C-Tick , EAC , NOM	
	Related Products	L8139D 10/100M Network Adapter S16 16-Port 10/100Mbps Desktop Switch TEG1008D 8-Port Gigabit Desktop Switch	
	Compatible OS	Windows 8 32/64 bit , Windows 7 32/64 bit , Windows xp 32/64 bit , Linux , MAC OS	
	Package Contents	5-Port 10/100Mbps Ethernet Switch Power Adapter (5V0.6A) Quick Installation Guide	8-Port 10/100Mbps Ethernet Switch Power Adapter (5V0.6A) Quick Installation Guide
	Packing (Qty)	Package Size: 89mm*65mm*98mm Carton size: 543mm*465mm*515mm Packing number: 200 PCS	Package Size: 130mm*77mm*78mm Carton size:560mm*540mm*415mm Packing number: 140 PCS
	Weight	NW/GW: 0.120KG / 0.160KG Carton Weight: 33KG	NW/GW: 0.144KG / 0.190KG Carton Weight: 28KG

**Note:** "Net" is the total weight of device itself and the power adapter (Europe).  
Adapter weight differs from different districts. The datasheet reserves the changes.

### SHENZHEN TENDA TECHNOLOGY CO., LTD.

Tenda Technology Bldg. Int'l E-City, # 1001 Zhong Shan Yuan Rd. ,Nanshan District, Shenzhen 518055,China

Phone: (86 755) 2765 7180 Fax:(86 755) 2765 7178

Email: sales@tenda.com.cn support@tenda.com.cn

Http: www.tendacn.com



© 2013 SHENZHEN TENDA TECHNOLOGY CO.,Ltd, the Tenda logo is registered trademark of Shenzhen Tenda Technology Co.,Ltd in China and/or other countries. Other brand and product names are trademarks or registered trademarks of their respective holders. Information is subject to change without notice. ALL rights reserved.