

PRODUCT DATASHEET

SENSOR WALL 110DEG IP44 WT

SENSOR WALL 110DEG | Stand-alone motion and light sensors for wall mounting with 110° detection range



AREAS OF APPLICATION

- Outdoor
- Corridors, entrance areas
- Garages
- Basement
- Arcade passage

PRODUCT BENEFITS

- Sensor for optimized energy savings

PRODUCT FEATURES

- Switch-on by movement
- Type of protection: IP44
- Protection class: II



TECHNICAL DATA


Electrical data

Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Luminaire sensor data

Type of sensor	Light / Motion
Sensor technology	Passive infrared (PIR)
Sensor detection angle	110 °
Detection range of motion sensor	12 m
Detection threshold of daylight sensor	1...1000 lx
Sensor controlled switching time	2 s...15 min

Dimensions & weight



Length	60.0 mm
Width	77.0 mm
Height	72.0 mm
Product weight	89.00 g

Colors & materials

Body material	Polycarbonate (PC)
Product color	White

Temperatures & operating conditions

Ambient temperature range	-10...+40 °C
---------------------------	--------------

Additional product data

Mounting type	Surface
Mounting location	Wall

Capabilities

Dimmable	No
Type of connection	Screw terminal, 3-Pole

Certificates & standards

Protection class	II
Type of protection	IP44
Standards	CE/EAC/REACH/RoHS

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075244733	Folding carton box 1	67 mm x 80 mm x 94 mm	112.00 g	0.50 dm ³
4058075244740	Shipping carton box 8	170 mm x 144 mm x 204 mm	1273.00 g	4.99 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

- Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.