

MIOMIX 104

5-Channel Professional Audio Mixer with Digital Echo Effect

MioMix 104 is a 5-channel mixer ideal for small home recording, live gigs and Podcasting applications that require professional quality level and maximum portability. The Mic input is equipped with a noise-less preamp, able to manage all main sound sources, such as condenser microphones - thanks to the +48V Phantom Power, dynamic mics, line and high-impedance inputs (guitars, basses, etc.). The stereo line inputs allow you to connect keyboards, CD players, DJ consoles, tablets, smartphones, etc. The professional echo digital effect enriches your performance by allowing you to adjust speed and number of repetitions. An indispensable and reliable tool for all small audio applications.



€ 75,00

including VAT



KEY FEATURES

5 Total Channels

1 Mic/Line channel with noiseless preamp, combo connector, Hi-Z input for guitars, +48V Phantom Power, Peak Indicator

1 Stereo Line Channel with ¼" Jack inputs, +4/-10dB Pad Adapter and Peak Indicator

1 Stereo Line Channel with RCA and 1/8" Stereo Mini-Jack

2-Band EQ on channels from 1 to 3

Digital Echo Effect with Repetition, Delay and Level adjustment

Headphone monitor out with level control

XLR Main Outputs with Master Level Control

Stereo 6-Led VU Meter Bar

Rugged and Lightweight Metal Case for Maximum Flexibility and Portability

MORE SPECIFICATIONS

Input Connections	Balanced XLR/Jack Combo (Channel 1). Balanced ¼" Jack (Channel 2-3). Stereo RCA, Stereo 1/8" Mini-Jack (Channel 4-5)
Output Connection	Balanced XLR (Main Out L-R). Stereo ¼" Jack (Phones)
Channel 1 Functions	+48V Phantom Power, Impedance switch (Line/Hi-Z), 2-Band EQ (80Hz/12kHz +/-15dB), Effect Send Level, Pan Position, Channel Volume, Peak Led Indicator
Channel 2-3 Functions	Impedance switch (+4/-10dB), 2-Band EQ (80Hz/12kHz +/-15dB), Effect Send Level, Pan Position, Channel Volume, Peak Led Indicator
Channel 4-5 Functions	Pan Position, Channel Volume
Effect Functions	Echo Repetition Adjustment, Echo Delay Time Adjustment, Echo Level Adjustment
Level Meter	2x6 LED Meter
Max Output Level	3 Vrms
Frequency Response	+/-0.5dB, 20Hz-20kHz
Dynamic Range	102dB
THD+N @ 1kHz	=0.003%
Stereo Crosstalk	92dB
Power Requirements	DC 5V, 0.5A
Power Consumption	Max. 2.5W
Net Weight	0.89kg