



# 18V Blower BL LXT

## DUB184Z

DUB184 is a cordless blower powered by 18V LXT Li-Ion battery



### TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Max air velocity	52.1 m/sec
Max air volume	13.0 m <sup>3</sup> /min
Noise sound pressure	86.6 dB(A)
Noise sound power	93.5 dB(A)
Noise K factor	2.7 dB(A)
No Load Speed	0 - 18,000 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	2.5 - 3.0 kg

### USER BENEFITS

- Variable speed
- Brushless motor
- Lock-on function
- Cruise control function: Cruise control lever allows you to lock the variable speed control trigger at the desired power level.
- Constant speed control
- Best grip to frame angle provides optimum nozzle to ground angle for efficient sweeping operation

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recon

## ■ OTHER