

# 40Vmax Hedgetrimmer 60cm XGT UH004GZ

Cordless Hedge Trimmer powered by 40Vmax Li-ion battery.



## TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	40 v
Strokes per Minute	2,000 / 3,600 / 5,000 spm
Blade Length	600 mm
Max Branch Diameter	23.5 mm
Noise sound pressure	85 dB(A)
Noise sound power	96 dB(A)
Noise K factor	3 dB(A)
Blade type	Double Sided
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Right Handle (Rear grip)	2.5 m/sec <sup>2</sup>
Vibration: Left Handle (Front grip)	2.9 m/sec <sup>2</sup>
Net weight	4.3 – 4.9 kg

## USER BENEFITS

- Brushless motor
- Constant speed control
- Electric brake
- Electronic 3-speed selection
- Reverse switch to free the blade when it is jammed by thick branches
- IPX4 level water resistant
- Sharp edge curved blade: ideal for trimming
- Inclined tooth edge enables the blade to easily catch, firmly hold and sharply cut twigs or thin branches
- Curved teeth reduce friction resistance to suppress energy loss
- Front handle switch
- Rubberised soft grip
- Low Vibration.

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recon

## ■ OTHER