

Panther Compact



The Panther Compact 30 White ABS 30W Round Horn Loudspeaker Designed for internal or external use, having an IP56 rating with stainless steel brackets.

- 30 watt rms, 100 volt line, ABS horn loudspeaker.
- 30 watt, 15 watt, 10 watt, 5 watt, 3 watt and 1 watt power tapings.
- IP56 rating for external use.
- Supplied with stainless steel bracket.

Technical Specification

Order Code	04-0003-C09
Connections:	Black - Common / Red - 100V
Model:	Panther 30 Compact
Power Taps:	30, 15, 10, 5, 3, 1w
Power Output (RMS):	30w rms
Line Voltage:	100v / 70v
Frequency Response:	400 - 10k Hz
Sensitivity:	106 +-3dB
IP Rating:	IP56
Material:	ABS
Weight:	1.8 kg
Total length of horn:	207.5mm
Diameter:	14.15 CM (141.5mm)in/cm