

Titan - 50W 100V IP65 Rectangular Music Horn



A 50W, 100V line, music horn loudspeaker, weather resistant to IP65.
Ideal for all music and speech reproduction in sports stadia and other outside venues.
Complies with 93/68/EEC. Frequency Response 90Hz - 20kHz. Sensitivity 93 +/- 3 dB.

Technical Specification

Power Taps	100V - 50W, 25W & 8 Ohm 70V - 50W, 25W, 12.5W & 8 Ohm
Speaker unit	165mm
Frequency Response	90Hz - 20kHz
Sensitivity	99 +/- 3 dB at 1W/1m
Mounting Size	363 x 253 x 310mm
Material	Plastic
Colour	White
Weight	4.5kg

Product Code : 04-0021-C09

