

2.5" HDD/SSD SATA Hot-Swap mobile rack for 9.5mm ultra slim optical bay

Fit perfectly into any 9.5mm ultra slimline optical bay



Designed for Desktop PCs



Aluminum Frame

Supports 5-7mm drive height

Supports both 2.5" SSD & HDD



Exact same dimension & port location

Interchangeable



EZ-Slide Slim Tray



ToughArmor MB411SPO-2B Features & Specs

- Exact same form factor of a ultra slimline optical drive.
- Fits 1 x 5mm to 7mm height 2.5" SAS / SATA HDD / SSD in a 9.5mm ultra slim ODD bay.
- Supports transfer speed up to 6Gbps (SAS host is required for SAS drives).
- The receiving SATA connector rated for up to 10,000 drive insertions
- Removable EZ Slide Slim drive tray for easy maintenance.
- Heavy duty full metal construction design - perfect for enterprise applications
- Multi-Flow Technology provides excellent passive cooling
- Anti-Vibration Technology creates a safe environment for hard drives or SSDs
- Active Power Technology (APT) powers up individual LED if only there is drive installed in the drive bay
- EMI Grounding protects hard drives from electrical damage
- Ideal 2.5" drive mobile rack for system that has ultra slim ODD bay, including rackmounts, IPCs, desktop PCs, OEM / ODM systems, embedded control systems, and factory automation systems.
- Limited 3 year warranty to complement the typical warranty of a hard drive.

Model Number	MB411SPO-2B
Color	Black
Host Interface	1 x Slimline SATA 7pin
Drive Fit	Single 2.5" SATA HDD/SSD
Compatible 2.5" Drive Heights	5mm, 7mm
Device Fit	1 x Ultra Slim ODD Bay
Transfer Rate	Up to 6 Gb/sec. (depending on hard drive speed)
Power Input	1 x 13pin SATA Slimline connector
Insert & Extract connection Via	Direct SATA hard drive connection
Structure	Full metal
Drive Cooling	Metal heat dispersion
Power Indicator	Solid green LED
HDD Access Indicator	Flashing green LED
Dimension (L x W x H)	127.0 x 129.4 x 9.5mm
Weight	383g
Package Contents	Device, user manual and screws