

## DEKO-25TBK

Pair of 2.5" full-range compact loudspeaker, black

This full-range speaker for the fixed-installation market is the result of the perfect combination of elegant and refined design, compactness, and superior quality sound. It is made for any indoor environment (available in both black and white color) and it adapts to any domestic or non-domestic installation solution, such as multi-room audio systems, meeting sales, shops.

DEKO-25T compact series speakers feature a 2.5" (63mm approx.) full-range transducer with high dynamic excursion, and reinforced paper cone. Also include a 100V line transformer for quick integration into constant voltage lines. The 100V power tap is 6W@100V; maximum power is 30W. The compact size of this woofer let us make a speaker of only 87x94x94mm, able to integrate into any interior without compromising sound quality.

Whether it is a domestic environment or a bar or shop, if combined with one or more subwoofers with a cut around 120-150Hz, it is possible to obtain an excellent result in terms of coverage and audio quality.



## PRODUCT DETAILS

### Key features

Compact and lightweight, suitable for any environment

Bracket with horizontal and vertical angle adjustable by +/- 30°

Superior sound with wide coverage

Built-in 100V line transformer

Easy installation thanks to the included bracket

Black Color

### Specifications

#### Full-range speaker

<b>Power RMS/Peak (100V)</b>	6W/30W
<b>Frequency response</b>	100Hz - 20kHz (±3dB)
<b>Sensitivity</b>	90dB (1W@1m)
<b>Coverage</b>	175° (HxV)
<b>Woofers</b>	2.5" Paper Cone, Full-Range
<b>Housing</b>	ABS with Metal Grille
<b>Speaker Size (WxDxH)</b>	94x87x94mm (bracket not included); 94x87x135 (max., with bracket, 0° angle)
<b>Bracket Size (WxDxH)</b>	55x55x45mm
<b>Speaker Weight</b>	0.503kg (single speaker with bracket)
<b>Color</b>	Black
<b>Carton Size (WxDxH)</b>	180x125x255mm (including 2 speakers and 2 brackets)
<b>Carton Weight</b>	1kg