

DEKO-25TWH

Pair of 2.5" full-range compact loudspeaker, white

This full-range speaker for the fixed-installation market is the result of the perfect combination of elegant and refined design, compactness, and superior sound quality. It is made for any indoor environment (available in both black and white color) and it adapts to any installation solution, such as multi-room audio systems, meeting sales, shops.

DEKO-25T compact series speakers feature a 2.5" (63mm approx.) full-range transducer with high dynamic excursion, and reinforced paper cone. Also include a 100V line transformer for quick integration into constant voltage lines. The 100V power tap is 6W@100V; maximum power is 30W. The compact size of this woofer let us make a speaker of only 87x94x94mm, able to integrate into any interior without compromising sound quality.

Whether it is a domestic environment or a bar or shop, if combined with one or more subwoofers with a cut around 120-150Hz, it is possible to obtain an excellent result in terms of coverage and audio quality.



PRODUCT DETAILS

Key features

Compact and lightweight, suitable for any environment

Bracket with horizontal and vertical angle adjustable by +/- 30°

Superior sound with wide coverage

Built-in 100V line transformer

Easy installation thanks to the included bracket

White Color

Specifications

Full-range speaker

Power RMS/Peak (100V)	6W/30W
Frequency response	100Hz - 20kHz (±3dB)
Sensitivity	90dB (1W@1m)
Coverage	175° (HxV)
Woofers	2.5" Paper Cone, Full-Range
Housing	ABS with Metal Grille
Speaker Size (WxDxH)	94x87x94mm (bracket not included); 94x87x135 (max., with bracket, 0° angle)
Bracket Size (WxDxH)	55x55x45mm
Speaker Weight	0.503kg (single speaker with bracket)
Color	White
Carton Size (WxDxH)	180x125x255mm (including 2 speakers and 2 brackets)
Carton Weight	1kg