

ILP6060B042



The Wattage of the Variable High Performance+ panel can be adjusted from 9.5 to 32W in 1.5W steps to give a light output range from 1600 to 5600lm in cool white. Its market leading level of efficacy (175lm/W) offers savings in running cost against traditional 72W fluorescent fitting as well as many other LED panel. Its lightweight steel and PC design, with integrated non-flicker driver, means installation is simple and maintenance is minimal. With a wide range of lumen outputs It is an ideal solution for many applications: office, meeting rooms, corridors, schools/universities and retail premises.

### Details

<b>Barcode:</b>	5055788253099
<b>Category:</b>	Panels
<b>Range Name:</b>	High Performance+ Variable Wattage
<b>Product Type:</b>	600 x 600
<b>Product Body Finish:</b>	Matt white
<b>Market Segment:</b>	Commercial indoor
<b>Warranty (Years):</b>	5
<b>CE RoHS:</b>	Yes

### Physical Data

<b>Product Depth (mm):</b>	63
<b>Product Width (mm):</b>	596
<b>Product Weight (g):</b>	3500
<b>Optic:</b>	TP(b) rated Polycarbonate diffuser
<b>Material:</b>	Steel, Polycarbonate
<b>Construction:</b>	Folded Mild Steel and Polycarbonate diffuser
<b>Luminaire Fixing:</b>	Recessed in ceiling grid, surface mounted (additional surface mounting kit required)
<b>Panel Equivalent:</b>	The Luminaire is Class II
<b>Placement / Application:</b>	Indoor, General Lighting

### Electrical Data

<b>Power Consumption (w):</b>	9.5 to 32
<b>Power Factor:</b>	0.9
<b>Wattage equivalent (W):</b>	86.4
<b>Amperage (mA):</b>	200
<b>Dimming:</b>	Non-Dimmable

<b>Driver Included:</b>	Integrated
<b>Electric Current:</b>	AC
<b>EN:</b>	EN-60598
<b>LVD Certified:</b>	Yes

## Light Data

<b>Luminous Flux in Lumens (lm):</b>	1600-5600
<b>Luminous efficacy (lm/W):</b>	168-179
<b>Lumens Range:</b>	Lumen Select - 1600 to 5600lm
<b>Correlated Colour Temperature (CCT) (K):</b>	4000
<b>Colour Temperature:</b>	4000K - Cool White
<b>Colour Temperature Name:</b>	Cool White
<b>Beam Angle:</b>	110
<b>Colour Rendering Index (CRI):</b>	80
<b>Frequency Range (Hz):</b>	50/60
<b>Instant on (Less than 1 second):</b>	Yes
<b>LED Size (mm):</b>	2835
<b>LED Type:</b>	Back-lit
<b>Lifetime (hours):</b>	50000
<b>Lighting Method:</b>	Back-lit
<b>Switching Cycles:</b>	25000

## Environment

<b>EN:</b>	EN-60598
<b>LVD Certified:</b>	Yes
<b>CE RoHS:</b>	Yes
<b>Hg 0% (Mercury Free):</b>	Yes
<b>IP Rating (Back/Recessed side):</b>	IP20
<b>IP Rating (Ingress Protection):</b>	IP20
<b>Lowest Operating Temperature (°C):</b>	-10
<b>Maximum Operating Temperature (°C):</b>	40
<b>TP rating:</b>	TP(b)

## Packaging

<b>Package Weight (g):</b>	4000
<b>Package Length (mm):</b>	630
<b>Package Width (mm):</b>	615
<b>Package Depth (mm):</b>	80