



### PIR SENSOR PRO

<p>V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.</p>

*One brand, endless solutions..*

SKU: 20258 - 930 938

[View more details](#)

### TECHNICAL INFORMATION

Watts:	10
Lumens:	735
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Diecast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	6500K
Dimension:	133x60x113mm
Sensor Type:	PIR
Detection Distance:	3-10m (Radius)



### FEATURES

- High quality Slim series PIR Sensor Foodlight
- Designed with high efficiency LED Samsung Chips
- Detects motion within a radius of 3 to 10 Meter
- Installing Height 1.8 Meter to 2.5 Meter
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



### PACKAGING

Gross Weight (Kgs): 0.33  
Unit CBM: 0.001325  
Dimension: 133x60x113mm

### MASTER BOX PACKAGING

Box Qty: 20  
Length (Box) mm: 138  
Width (Box) mm: 63  
Height (Box) mm: 118

### LISTING DETAILS

Ean Code: 3800157661164