



PIR SENSOR PRO

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20273 - 931 940

[View more details](#)

TECHNICAL INFORMATION

| | |
|------------------------|-------------------|
| Watts: | 20 |
| Lumens: | 1510 |
| Input Power: | AC:220-240V, 50Hz |
| Long Life: | 25,000 Hours |
| Unit Color: | White |
| Body Type: | Diecast Aluminium |
| PF: | >0.9 |
| LED Chip Type: | SMD-Samsung Chip |
| CRI: | >80 |
| Operation Temperature: | -20°C to +40°C |
| Dimmable: | No |
| Beam Angle: | 100° |
| Color Temperature: | 6500K |
| Dimension: | 157x60x128mm |
| Sensor Type: | PIR |
| Detection Distance: | 3-10m (Radius) |



SMD LED'S



5 YEAR WARRANTY

85% ENERGY SAVING



IP65
RATING



5 YEAR
WARRANTY



CRI>80



SAVE UP TO
85%
ENERGY

FEATURES

- High quality Slim series PIR Sensor Foodlight
- Designed with high efficiency LED Samsung Chips
- Detects motion within a radius of 3 to 10 Meter
- Installing Height 1.8 Meter to 2.5 Meter
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



PACKAGING

Gross Weight (Kgs): 0.43
Unit CBM: 0.001728
Dimension: 157x60x128mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 162
Width (Box) mm: 63
Height (Box) mm: 133

LISTING DETAILS

Ean Code: 3800157661317