



PIR SENSOR PRO

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand. endless solutions..

SKU: 20283 - 931 938

[View more details](#)

TECHNICAL INFORMATION

Watts:	20
Lumens:	1510
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Diecast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	3000K
Dimension:	157x60x128mm
Sensor Type:	PIR
Detection Distance:	3-10m (Radius)



IP65
RATING



5 YEAR
WARRANTY



CRI>80



SAVE UP TO
85%
ENERGY

FEATURES

- High quality Slim series PIR Sensor Floodlight with 1 Meter cable
- Designed with high efficiency LED Samsung Chips
- Detects motion within a radius of 3 to 10 Meter
- Installing Height 1.8 Meter to 2.5 Meter
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



PACKAGING

Gross Weight (Kgs): **0.5**
Unit CBM: **0.00172**
Dimension: **157x60x128mm**

MASTER BOX PACKAGING

Box Qty: **20**
Length (Box) mm: **162**
Width (Box) mm: **63**
Height (Box) mm: **133**

LISTING DETAILS

Ean Code: **3800157661416**