

# E-VOL120

100 volt, 120 watts Euro volume control, white



The E-VOL120 is a 100 volt volume control that can handle up to 120 watts of power. It is very versatile thanks to the step-by-step attenuation in 11 steps + zero position. The E-VOL 120 is designed to handle 24V priority signals. This means that you can always get an announcement out, even to zones where the local volume control is in the 'OFF' position!

If your amplifier has a 24V priority output, it will send a 24V signal when you push the talk button on the microphone.

The 24V signal will close a relay on the E-VOL120 volume control, and the signal will pass, even when the volume control is in the 'OFF' position. This can be very useful for emergency or evacuation messages. The E-VOL120 is built on a universal chassis that easily can be integrated with Gira, Jung and Euro.

## TECHNICAL SPECIFICATIONS

stereo/mono	mono	applicable low impedance	No
applicable 100V	Yes	max. power in watts	120
steps	0 + 11	24 volt priority relais	Yes
mounting	screw	connector type	euroblock 6-pole
max. cable in mm <sup>2</sup>	2.5	width in mm	80
height in mm	80	depth in mm	50
weight in gr	336	Net weight product (kg)	0,40

MORE PICTURES



**ACCESSORIES****E-MODON**

Built-on box for wall controls