



- Screwless Plate
- Double Pole Switching
- Fitted With Fused Link
- Fully Rated to 13A
- Satin Chrome Finish

**Product Specification Data**

Revision Date: 15/10/2021

Product Standard/s	BS 1363-4
Terminal Capacity L&N	3 x 1.5, 3 x 2.5, 2 x 4.0 mm <sup>2</sup>
Terminal Capacity E	1 x 1.5, 1 x 2.5 Solid, 1 x 0.5, 1 x 1.5 Flex mm <sup>2</sup>
Frequency	50 Hz
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes
Wiring system	2-pole switch
Method of operation	Rocker/button
Assembly arrangement	Control element
Number of modules (module system)	0
Push button switch	Yes
Number of rockers	1
Mounting method	Flush mounted (plaster)
Type of fastening	Screw mounting
With mounting plate	Yes
Material	Metal
Material quality	Other
Halogen free	Yes
Surface protection	Other
Surface finishing	Matt
Colour	Stainless Steel
Illumination	No
Function lighting	Other
Type of lighting	Not included
Suitable for degree of protection (IP)	IP2X
Nominal voltage	250 V
Rated current	13 A
Connection type	Screwed terminal

Width of device	88 mm
Height of device	88 mm
Depth of device	29 mm
Built-in depth	17 mm
Min. depth of built-in installation box	25 mm

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.