

EDIFIER®

R1280DBs

Multi-media 2.0 Speakers



Features

- Qualcomm Bluetooth V5.0 for stable wireless connection
- Wooden enclosure isolates acoustic resonance and creates a classic look
- Studio tuned sound from silk dome tweeter and 4-inch bass driver
- 42 watts RMS total power for distortion-free listening
- Audio inputs: Bluetooth, Optical, Coaxial and dual RCA inputs
- Side panel control and wireless remote included
- Sub-out output works with external subwoofer
- Front-facing bass reflex port for punchy bass

Specifications

RMS	: R/L : 21W+21W
Driver Unit	: Φ13mm tweeter unit + 4-inch mid-woofer
Bluetooth	: QCC3003/V5.0
Signal Noise Ratio	: ≥85dB (A)
Input Sensitivity	: LINE IN1 R/L:500±50mV LINE IN2 R/L:600±50mV Optical /Coaxial R/L:350±50mFFS Bluetooth R/L:700±50mFFS
Frequency Response	: 51Hz-20KHz
Input Interface	: LINE IN 1、LINE IN 2、 Optical、 Coaxial、 Bluetooth

Package Info

Inner Carton	431mm x 300mm x 183mm(LxWxH),5.5kg(gross weight)
Master Carton	449mm x 314mm x 384mm(LxWxH),11.7kg(gross weight)
PCS/CTN	2

Color Options	EAN code
■ Black	6923520268429
■ Brown	6923520268436