

Cooker Connection Unit

45 AMP



K5045WHI

Cooker Controls

 MOULDED FLUSH
 45 AMP


K5060WHI



K5061WHI

 MOULDED SURFACE
 45 AMP


K5040WHI



K5041WHI

 METAL FLUSH
 45 AMP


K5011WHI

 METAL SURFACE
 45 AMP


K5001WHI

K5045WHI

10

MOUNTING BOX
FLUSH

877ZIC (46mm)

 Supplied complete with terminal block, each terminal of which will accommodate up to two 10mm² conductors.

Moulded cover plate, cable clamp included.

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS EN 60670-22:2006

K5060WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET

K5061WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET WITH NEONS

MOUNTING BOXES
FLUSH
886ZIC (6mm² conductors)878ZIC (10mm² conductors)

Rotary operated shutter.

DIMENSIONS

86 x 146mm

FIXING CENTRES

120.6mm

BS 4177:1992

K5040WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET

K5041WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET WITH NEONS

Supplied complete with mounting box and cable restraint.

Fitted with earth terminals.

Rotary operated shutter.

DIMENSIONS

86 x 146 x 60mm

BS 4177:1992

K5011WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET WITH NEONS

MOUNTING BOX
FLUSH

5120ALM

Fitted with earth terminals.

Rotary operated shutter.

DIMENSIONS

178 x 165mm

BS 4177:1992

K5001WHI

1

45A DP MAIN SWITCH AND 13A SWITCHSOCKET OUTLET WITH NEONS

Supplied complete with mounting box.

Fitted with earth terminals.

Rotary operated shutter.

DIMENSIONS

156 x 144 x 67mm

KNOCKOUTS

5 x 25mm.

Two in each of top and bottom, one in back.

BS 4177:1992