

## STILE 550

Cardioid Gooseneck Microphone - 55cm length, Black

STILE 450-550 Series Goose-neck Microphones deliver high-level performance, control, and flexibility for meetings and conferences.

High quality cartridges with **cardioid polar pattern** deliver accurate voice capture with **minimum pickup of room noise**.

**Dual bend** at bottom and top allow precise placement in meetings and conferences. A choice of 45 cm (17.7 inch) and 55 cm (21.6 inch) lengths, with or without on/off switch, match different table dimensions or seating configurations.



## PRODUCT DETAILS

### Key features

55 cm (21.6 inch) length, black finish

Designed for high-quality sound capture in meetings and conferences

Reference sound-receiving distance 30-40 cm

Gooseneck bends at bottom and top

Accept Phantom Power from 9V to 52V

Foam windscreen included

Works with STILO B200/S mic bases

### Specifications

<b>Element</b>	Condenser (Back Electret)
<b>Polar pattern</b>	Cardioid (Direzionale)
<b>Reference sound-receiving distance</b>	30-40 cm
<b>Frequency response</b>	50Hz-18kHz
<b>Sensitivity</b>	-45dB (1v @ 1pa)
<b>Impedance</b>	600ohms
<b>Max input SPL</b>	123dB (1kHz @ 1% T.H.D)
<b>S/N ratio</b>	70dB, 1kHz @ 1pa
<b>Phantom power requirement</b>	9-52V DC
<b>Microphone Size</b>	550 x Ø13mm
<b>Microphone Weight</b>	130g
<b>Wind-screen size</b>	40 x Ø32mm
<b>Packing Size</b>	600 x 30 x 30mm
<b>Packing Weight</b>	0,16kg